

Part Number	Part Description	Liquid/ Powder
10012011	MEDIUM199 HANKSW/25MM HEPE(CE)	Powder
10012037	MEDIUM199 HANKSW/25MM HEPE(CE)	Powder
11058021	OPTI MEM I	Liquid
11058021	OPTI MEM I	Liquid
11058022	OPTI MEM I	Liquid
11220035	WAYMOUTHS MB 752 1 MED	Liquid
11220098	WAYMOUTHS MB 752 1 MED	Liquid
11360039	SODIUM PYRUVATE MEM 100MM(CE)	Liquid
11360070	SODIUM PYRUVATE SOL	Liquid
11360097	SODIUM PYRUVATE SOL	Liquid
11700077	MEM EARLES	Powder
11700077	MEM EARLES	Powder
11900016	MEM ALPHA W/NUCLEOSIDES	Powder
11900024	MEM ALPHA	Powder
11900073	MEM ALPHA	Powder
11900073	MEM ALPHA	Powder
12000014	MEM ALPHA W/O NUCLEOSIDES	Powder
12000022	MEM ALPHA	Powder
12000063	MEM ALPHA	Powder
12000063	MEM ALPHA	Powder
12100046	DMEM	Powder
12100061	DMEM	Powder
12200036	IMDM	Powder
12200069	IMDM	Powder
12400024	DMEM NUTRIENT MIX F12	Powder
12500062	DMEM NUTRIENT MIX F12	Powder
12500096	DMEM NUTRIENT MIX F12	Powder
12551032	WILLIAMS MED E	Liquid
12551098	WILLIAMS MED E	Liquid
12591038	BGJB MED	Liquid
12591098	BGJB MED	Liquid
12800017	DMEM	Powder
12800082	DMEM	Powder
13018015	RPMI 1640 W/25MM HEPES (CE)	Powder
13018031	RPMI 1640 W/25MM HEPES (CE)	Powder
21300017	P.B.S. (DULBECCO'S)	Powder
21300025	DPBS	Powder
21300058	DPBS	Powder
21300058	DPBS	Powder
21300074	DPBS	Powder
21600010	DPBS	Powder
21600044	DPBS	Powder
21600069	DPBS	Powder
21700018	F 12 NUTRIENT MIX, HAMS	Powder

21700018	F 12 NUTRIENT MIX, HAMS	Powder
21700026	NUTRIENT MIXTURE F-12 (HAM)	Powder
21700075	F 12 NUTRIENT MIX, HAMS	Powder
22100093	GMEM	Powder
22551022	WILLIAMS' MEDIUM E (CE)	Liquid
22600050	OPTI MEM I	Powder
22600134	OPTI MEM I	Powder
22600134	OPTI MEM I	Powder
23400021	RPMI 1640	Powder
23400062	RPMI 1640	Powder
31100019	MED 199 EARLES	Powder
31100019	MED 199 EARLES	Powder
31100027	MEDIUM 199 W/EBSS	Powder
31100035	MED 199 EARLES	Powder
31220023	WAYMOUTH MEDIUM MB 752/1 (CE)	Liquid
31600034	DMEM	Powder
31600083	DMEM	Powder
31600083	DMEM	Powder
31600091	DMEM	Powder
31600091	DMEM	Powder
31800022	RPMI 1640	Powder
31800089	RPMI 1640	Powder
31800105	RPMI 1640	Powder
31985047	OPTIMEM 1 (CE)	Liquid
31985062	OPTI MEM I	Liquid
31985070	OPTI MEM I	Liquid
31985088	OPTI MEM I	Liquid
31985097	OPTI MEM I	Liquid
32500035	DMEM/F12 (1:1) W/L-GLUT (CE)	Powder
32500043	DMEM/F12 (1:1) W/L-GLUT (CE)	Powder
32500050	DMEM/F12 (1:1) W/L-GLUT	Powder
32551020	WILLIAMS E W/GLUTAMAX-I	Liquid
41300021	LEIBOVITZ'S L-15 MEDIUM	Powder
41300039	LEIBOVITZ L 15 MED	Powder
41300070	LEIBOVITZ L 15 MED	Powder
41300070	LEIBOVITZ L 15 MED	Powder
41500018	MEM EARLES NEAA	Powder
41500018	MEM EARLES NEAA	Powder
41500034	MEM EARLES NEAA	Powder
41500067	MEM W/EBSS W/NEAA	Powder
41500083	MEM EARLES NEAA	Powder
41500083	MEM EARLES NEAA	Powder
42200014	ISCOVE MOD.DULBECCO (IMDM)(CE)	Powder
42200030	ISCOVE MOD.DULBECCO (IMDM)(CE)	Powder
42400010	DUL MEM/NUTMIX F12 W/HEPES(CE)	Powder
42400028	DUL MEM/NUTMIX F12 W/HEPES(CE)	Powder
51800019	RPMI-1640 MEDIUM (CE)	Powder

51800035	RPMI-1640 MEDIUM (CE)	Powder
51800043	RPMI-1640 MEDIUM (CE)	Powder
51985026	OPTIMEM-I W/GLUTAMAX-I (CE)	Liquid
51985034	OPTI MEM I W/GLUTAMAX-I	Liquid
51985091	OPTI MEM I W/GLUTAMAX-I	Liquid
61100053	MEM W/EBSS	Powder
61100061	MEM EARLES	Powder
61100087	MEM EARLES	Powder
61100087	MEM EARLES	Powder
61100103	MEM EARLES	Powder
61100103	MEM EARLES	Powder
11012044	MEM W/HBSS W/25MM HEPES	Powder
52100021	D-MEM (HG) W/O PYRUVATE (CE)	Powder
52100039	D-MEM (HG) W/O PYRUVATE (CE)	Powder
52100047	D-MEM (HG) W/O PYRUVATE (CE)	Powder