ALFAAA17659

2-Undecanone

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:	2-十一(烷)酮
Product Description:	**2-Undecanone**
Cat No. :	**A17659**
Synonyms	Methyl nonyl ketone
CAS No	112-12-9
Molecular Formula	C11 H22 O
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11 Emergency Number **US:**001-201-796-7100 / **Europe:** +32 14 57 52 99 **CHEMTREC** Tel. No. **US:**001-800-424-9300 / **Europe:**001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State	**Appearance**	**Odor**
Liquid	Light yellow	No information available

Emergency Overview
Combustible liquid. Very toxic to aquatic life with long lasting effects.

Classification of the substance or mixture

Flammable liquids.	Category 4
Acute aquatic toxicity	Category 1
Chronic aquatic toxicity	Category 1

Label Elements

Signal Word **Warning**

Hazard Statements
H227 - Combustible liquid
H410 - Very toxic to aquatic life with long lasting effects

Precautionary Statements
Prevention
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P280 - Wear protective gloves/protective clothing/eye protection/face protection
Response
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
Storage
P403 + P235 - Store in a well-ventilated place. Keep cool
Disposal
P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards
Combustible material.
Health Hazards
The product contains no substances which at their given concentration are considered to be hazardous to health.
Environmental hazards
Very toxic to aquatic life with long lasting effects. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product is insoluble and floats on water. The product evaporates slowly.

Other Hazards

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
2-Undecanone	112-12-9	>95

SECTION 4. FIRST AID MEASURES

General Advice
If symptoms persist, call a physician.

Eye Contact
Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact
Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation
Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion
Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects
None reasonably foreseeable. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider
Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician
Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media
Water spray, carbon dioxide (CO2), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons
No information available.

Specific Hazards Arising from the Chemical
Combustible material. Containers may explode when heated. Do not allow run-off from fire-fighting to enter drains or water courses.

Protective Equipment and Precautions for Firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions
Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions
Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

Methods for Containment and Clean Up
Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling
Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition.

Storage
Keep away from heat, sparks and flame. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)
Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Monitoring methods
BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

Exposure Controls

Engineering Measures
Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the

workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.
Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)
Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.
Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Light yellow	
Physical State	Liquid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	11 - 13 °C / 51.8 - 55.4 °F	
Softening Point	No data available	
Boiling Point/Range	231 - 232 °C / 447.8 - 449.6 °F	@ 760 mmHg
Flash Point	88 °C / 190.4 °F	**Method -** No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	<1 mmHg @ 20 °C	
Vapor Density	5.9	(Air = 1.0)
Specific Gravity / Density	0.824	
Bulk Density	Not applicable	Liquid
Water Solubility	Insoluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		

Component	**log Pow**
2-Undecanone	4.09

Autoignition Temperature No data available
Decomposition Temperature No data available
Viscosity No data available
Explosive Properties explosive air/vapour mixtures possible
Oxidizing Properties No information available

Molecular Formula C11 H22 O
Molecular Weight 170.3

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.

Hazardous Reactions None under normal processing.
Hazardous Polymerization No information available. Hazardous polymerization does not occur.

Conditions to Avoid Incompatible products. Keep away from open flames, hot surfaces and sources of ignition.

Materials to avoid Strong oxidizing agents. Strong bases.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO_2).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
2-Undecanone	LD50 = 5 g/kg (Rat)	LD50 > 2 g/kg (Rabbit)	

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;
Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; No data available

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects,both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects The product contains following substances which are hazardous for the environment. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
2-Undecanone	LC50: 2.2 - 4.4 mg/L, 96h flow-through (Oncorhynchus mykiss) LC50: 1.39 - 1.62 mg/L, 96h flow-through (Pimephales promelas) LC50: 1.6 - 3.1 mg/L, 96h flow-through (Lepomis macrochirus)	EC50: 0.54 mg/L, 48h		

Persistence and Degradability

Persistence Insoluble in water, May persist, based on information available.

Degradation in sewage treatment plant Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential May have some potential to bioaccumulate; Product has a high potential to bioconcentrate

Component	log Pow	Bioconcentration factor (BCF)
2-Undecanone	4.09	No data available

Mobility in soil Spillage unlikely to penetrate soil The product is insoluble and floats on water The product evaporates slowly Is not likely mobile in the environment due its low water solubility Is not likely mobile in the environment due its low water solubility and propensity to bind to soil particles: Spillage unlikely to penetrate soil

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant This product does not contain any known or suspected substance

Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. Should not be released into the environment.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN3082
Proper Shipping Name	Environmentally hazardous substances, liquid, n.o.s.
Technical Shipping Name	2-Undecanone
Hazard Class	9
Packing Group	III

IMDG/IMO

UN-No	UN3082
Proper Shipping Name	Environmentally hazardous substances, liquid, n.o.s.
Technical Shipping Name	2-Undecanone
Hazard Class	9
Packing Group	III

IATA

UN-No	UN3082
Proper Shipping Name	Environmentally hazardous substances, liquid, n.o.s.
Technical Shipping Name	2-Undecanone
Hazard Class	9
Packing Group	III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories
X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
2-Undecanone	-	X	X	203-937-5	X	X	X	X	X	X	KE-35072

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By	Health, Safety and Environmental Department
Creation Date	24-Nov-2010
Revision Date	25-Jul-2026
Revision Summary	Not applicable.

Training Advice
Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.
Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit

and standards.
First aid for chemical exposure, including the use of eye wash and safety showers.
Chemical incident response training.

Legend

CAS - Chemical Abstracts Service
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
IECSC - Chinese Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
ENCS - Japanese Existing and New Chemical Substances
AICS - Australian Inventory of Chemical Substances
NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit
ACGIH - American Conference of Governmental Industrial Hygienists
DNEL - Derived No Effect Level
RPE - Respiratory Protective Equipment
LC50 - Lethal Concentration 50%
NOEC - No Observed Effect Concentration
PBT - Persistent, Bioaccumulative, Toxic
TWA - Time Weighted Average
IARC - International Agency for Research on Cancer
PNEC - Predicted No Effect Concentration
LD50 - Lethal Dose 50%
EC50 - Effective Concentration 50%
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association
ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road
OECD - Organisation for Economic Co-operation and Development
BCF - Bioconcentration factor
IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
MARPOL - International Convention for the Prevention of Pollution from Ships
ATE - Acute Toxicity Estimate
VOC - (Volatile Organic Compound)

Key literature references and sources for data
https://echa.europa.eu/information-on-chemicals
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet