

Explore our broad range of Phosphine Ligands

We offer a wide choice of Phosphine Ligands including monodentate, didentate and chiral phosphine ligands in a range of convenient pack sizes ideal for your synthetic chemistry research.

Our recently expanded range includes phosphonium hexafluoroborates and tetrafluoroborates, which offer air stable and safer to use alternatives to the pyrophoric trialkyl phosphines.

Discover our most recently added Phosphine Ligands shown below.

Product code	Product name	Pack size	CAS number
438640050	Chlorotripyrrolidinophosphonium hexafluorophosphate, 98%	5g	133894-48-1
438640250	Chlorotripyrrolidinophosphonium hexafluorophosphate, 98%	25g	133894-48-1
366940050	Tri-tert-butylphosphonium tetrafluoroborate, 97+%	5g	131274-22-1
386960010	Di-tert-butylmethylphosphonium tetrafluoroborate, 99%	1g	479094-62-7
386960050	Di-tert-butylmethylphosphonium tetrafluoroborate, 99%	5g	479094-62-7
386830010	Tricyclohexylphosphonium tetrafluoroborate, 99%	1g	58656-04-5
386830050	Tricyclohexylphosphonium tetrafluoroborate, 99%	5g	58656-04-5
389110010	Triethylphosphonium tetrafluoroborate, 99%	1g	
389110050	Triethylphosphonium tetrafluoroborate, 99%	5g	
386970010	Di-tert-butylphenylphosphonium tetrafluoroborate, 99%	1g	612088-55-8
386970050	Di-tert-butylphenylphosphonium tetrafluoroborate, 99%	5g	612088-55-8
366940010	Tri-tert-butylphosphonium tetrafluoroborate, 97+%	1g	131274-22-1
321560250	Bis(diisopropylamino)chlorophosphine	25g	56183-63-2
363700050	1,2-Bis(dipentafluorophenylphosphino)ethane, 95%	5g	76858-94-1
316830250	Tris[2-(diphenylphosphino)ethyl]phosphine, 97%	25g	23582-03-8
317330250	Triisopropylphosphine, 98%	25g	6476-36-4
140435000	Triphenylphosphine oxide, 99%	500g	791-28-6
438980050	Triphenyl(2-pyridylmethyl)phosphonium chloride hydrochloride, 98%	5g	99662-46-1
438980250	Triphenyl(2-pyridylmethyl)phosphonium chloride hydrochloride, 98%	25g	99662-46-1
435231000	1,2-Bis((2S,5S)-2,5-dimethylphospholano)ethane(cyclooctadiene)rhodium(II) tetrafluoroborate, 97%	100mg	213343-65-8
435235000	1,2-Bis((2S,5S)-2,5-dimethylphospholano)ethane(cyclooctadiene)rhodium(II) tetrafluoroborate, 97%	500mg	213343-65-8
435030025	2-(Di-tert-butylphosphino)ethylamine, 10 wt.% solution in THF	2.5mL	1053658-84-6
434141000	(1S,2S)-2-Amino-1-phenylpropyldiphenylphosphine, 97%	100mg	341968-71-6
434142500	(1S,2S)-2-Amino-1-phenylpropyldiphenylphosphine, 97%	250mg	341968-71-6
435160010	5-(Di-tert-butylphosphino)-1',3',5'-triphenyl-1'H-1,4-bipyrazole, 97%	1g	894086-00-1
434121000	(2S,5S)-1-(2-(1,3-Dioxolan-2-yl)phenyl)-2,5-diethylphospholane, 97%	100mg	1314246-02-0
434125000	(2S,5S)-1-(2-(1,3-Dioxolan-2-yl)phenyl)-2,5-diethylphospholane, 97%	500mg	1314246-02-0
435171000	(2S,5S)-1-(2-(1,3-Dioxolan-2-yl)phenyl)-2,5-dimethylphospholane, 97%	100mg	695816-47-8
435175000	(2S,5S)-1-(2-(1,3-Dioxolan-2-yl)phenyl)-2,5-dimethylphospholane, 97%	500mg	695816-47-8
434091000	(1S,2S)-2-(Diphenylphosphino)-1,2-diphenylethylamine, 97%	100mg	1091606-67-5
434092500	(1S,2S)-2-(Diphenylphosphino)-1,2-diphenylethylamine, 97%	250mg	1091606-67-5
434102500	(S)-2-((Diphenylphosphino)methyl)pyrrolidine, 97%	250mg	60261-46-3
434130010	3-(Diphenylphosphino)propylamine, 97%	1g	16605-03-1
434112500	(R)-8-(Diphenylphosphino)-1,2,3,4-tetrahydronaphthalen-1-amine, 97%	250mg	960128-64-7
437281000	(S,S)-[2-(4'-Isopropylloxazolin-2'yl)ferrocenyl]diphenylphosphine, 97%	100mg	163169-29-7
437282500	(S,S)-[2-(4'-Isopropylloxazolin-2'yl)ferrocenyl]diphenylphosphine, 97%	250mg	163169-29-7
435131000	2-(Bis(3,5-di-tert-butyl-4-methoxyphenyl)phosphino)benzaldehyde, 97%	100mg	1202865-21-1
435132500	2-(Bis(3,5-di-tert-butyl-4-methoxyphenyl)phosphino)benzaldehyde, 97%	250mg	1202865-21-1

Product code	Product name	Pack size	CAS number
435142500	2-(Bis(3,5-dimethylphenyl)phosphino)benzaldehyde, 97%	250mg	669091-00-3
435112500	(1R,2R)-N,N-Bis(2-(diphenylphosphino)benzyl)cyclohexane-1,2-diamine, 95%	250mg	174758-63-5
435155000	2-(Di-p-tolylphosphino)benzaldehyde, 97%	500mg	1202865-03-9
436461000	Trioctylphosphine, 90%, technical grade, AcroSeal™	100mL	4731-53-7
433621000	Lithium diphenylphosphide, 0.5M solution in THF, AcroSeal™	100mL	65567-06-8
429712500	1,1'-Bis(di-tert-butylphosphino)ferrocene, 98%	250mg	84680-95-5
429710010	1,1'-Bis(di-tert-butylphosphino)ferrocene, 98%	1g	84680-95-5
430000010	Di(1-adamantyl)-n-butylphosphine, 97%	1g	321921-71-5
430000050	Di(1-adamantyl)-n-butylphosphine, 97%	5g	321921-71-5
429840010	2-Di-tert-butylphosphino-2',4',6'-triisopropylbiphenyl, 97%	1g	564483-19-8
429840050	2-Di-tert-butylphosphino-2',4',6'-triisopropylbiphenyl, 97%	5g	564483-19-8
429830010	2-Dicyclohexylphosphino-2',6'-diisopropoxybiphenyl, 95%	1g	787618-22-8
429011000	Di-tert-butylphosphine, 0.5M (10 wt.%) solution in hexanes, AcroSeal™	100mL	819-19-2
429041000	Diisopropylphosphine, 10 wt.% solution in hexanes, AcroSeal™	100mL	20491-53-6
390250010	tert-Butyldicyclohexylphosphine, 97%	1g	93634-87-8
390250050	tert-Butyldicyclohexylphosphine, 97%	5g	93634-87-8
428421000	Tricyclohexylphosphine, 1M solution in toluene, AcroSeal™	100mL	2622-14-2
427660010	Diphenyl-2-pyridylphosphine, 97%	1g	37943-90-1
427660050	Diphenyl-2-pyridylphosphine, 97%	5g	37943-90-1
427840500	2-Chloro-5,5-dimethyl-1,3,2-dioxaphosphorinane, 97%, AcroSeal™	50mL	2428-06-0
427280500	Di-tert-butylchlorophosphine, 96%, AcroSeal™	50mL	13716-10-4
427831000	Tricyclohexylphosphine, 1M solution in THF, AcroSeal™	100mL	2622-14-2
427270500	Chlorodiisopropylphosphine, 96%, AcroSeal™	50mL	40244-90-4
426400010	2-(Diphenylphosphino)benzaldehyde, 97%	1g	50777-76-9
426530010	4-(Diphenylphosphino)benzoic acid, 97%	1g	2129-31-9
426530050	4-(Diphenylphosphino)benzoic acid, 97%	5g	2129-31-9
427290500	Diphenylphosphine, 95%, AcroSeal™	50mL	829-85-6
427301000	Tri-n-butylphosphine, 95%, AcroSeal™	100mL	998-40-3
427308000	Tri-n-butylphosphine, 95%, AcroSeal™	800mL	998-40-3
294800010	Tri-(2-furyl)phosphine, 98%	1g	5518-52-5
321470050	1,2-Bis(dichlorophosphino)ethane, 97%	5g	28240-69-9
363850010	1,2-Bis(dicyclohexylphosphino)ethane, 98%	1g	23743-26-2
363850050	1,2-Bis(dicyclohexylphosphino)ethane, 98%	5g	23743-26-2
363725000	(-)-1,2-Bis[(2R,5R)-2,5-diethylphospholano]benzene, 97%	500mg	136705-64-1
321560010	Bis(diisopropylamino)chlorophosphine	1g	56183-63-2
363870025	1,1'-Bis(diisopropylphosphino)ferrocene, 98%	2.5g	97239-80-0
310030010	1,2-Bis(dimethylphosphino)ethane, 97%	1g	23936-60-9
310030050	1,2-Bis(dimethylphosphino)ethane, 97%	5g	23936-60-9
320890050	cis-1,2-Bis(diphenylphosphino)ethylene, 98%	5g	983-80-2
310040050	trans-1,2-Bis(diphenylphosphino)ethylene, 97%	5g	983-81-3
316820050	Bis(2-diphenylphosphinoethyl)phenylphosphine, 97%	5g	23582-02-7
320850050	1,5-Bis(diphenylphosphino)pentane, 97%	5g	27721-02-4

Products are available in a variety of pack sizes. For more information please visit our web site www.acros.com or contact your local distributor.

Authorised distributor

In Australia:

For customer service, call 1300-735-292
To fax an order, use 1800-067-639
To email an order, ordersau@thermofisher.com

In New Zealand:

For customer service, call 0800-933-966
To fax an order, use 0800-329-246
To email an order, ordersnz@thermofisher.com

ThermoFisher
SCIENTIFIC

