



Ansell Glove Guide

ThermoFisher
SCIENTIFIC

Delivering the right solutions for the most demanding work

Partnering to protect

By leveraging off our world class expertise and knowledge, Thermo Fisher Scientific in collaboration with Ansell are working hard to deliver safety and productivity outcomes to workers around the world.

Over many years, our comprehensive understanding of the demands of scientific work has resulted in a range of solutions enabling greater comfort, performance and productivity that have significantly improved both worker safety and work quality.

Fit for purpose

Our product range includes some of the most trusted brands in hand protection from Ansell – TouchNTuff® and Microflex®, that offer a wide variety of solutions to meet your every need.

And it doesn't stop at hand protection – a full range of chemical and mechanical protection products are also readily available.

Need help?

Do you have questions on how best to solve a problem? Do you want to sample a product or compare several product types?

Then our team is happy to help.

Micro-Touch[®] NitraTex[®] 447

Powder free nitrile examination gloves



For patient contact when chemical protection is not required and latex allergies need to be avoided

- Nitrile gloves offering a comfortable fit and good grip
- Improved softer formula
- Ambidextrous
- Powder and latex free
- High tear resistance
- Silicone free – ensures no delamination to contaminate test results
- Thiurams and mercaptobenzothiazoles free – reduces the risk of contact dermatitis
- Textured fingers and palm for excellent grip
- Manufactured in accordance with ISO 13485
- Carries the CE mark and conforms to EN 455 – 1, 2 & 3

EN 374



Item No.	Product
ANS4470	Gloves Micro-Touch NitraTex small 100pcs
ANS4472	Gloves Micro-Touch NitraTex medium 100pcs
ANS4474	Gloves Micro-Touch NitraTex large 100pcs
ANS4476	Gloves Micro-Touch NitraTex ex-large 100pcs

Micro-Touch[®] DermaClean[®] 457

Powder free latex examination gloves



For patient contact when chemical protection is not required

- Powder free natural rubber latex that is easy to don, comfortable, soft and flexible
- Ambidextrous
- Thiurams and mercaptobenzothiazoles free – reduces the risk of contact dermatitis
- Textured surface for improved wet and dry grip
- Smooth chlorinated inner surface for improved donning
- Low allergenicity glove due to low chemical residues, latex protein (Total protein level 50ug/dm²) and the absence of powder

Item No.	Product
ANS4570	Gloves Micro-Touch DermaClean x-small 100pcs
ANS4572	Gloves Micro-Touch DermaClean small 100pcs
ANS4574	Gloves Micro-Touch DermaClean medium 100pcs
ANS4576	Gloves Micro-Touch DermaClean large 100pcs
ANS4578	Gloves Micro-Touch DermaClean x-large 80pcs

Microflex® 93-833

Certified ergonomic

Powder free nitrile gloves



Entry level lab glove for general chemical protection

- Ergonomically designed to reduce muscle effort and hand fatigue
- More comfortable and lighter weight glove versus most other examination gloves
- 0.07mm palm thickness and our advanced proprietary nitrile formulation delivers increased tactility
- Reliable durability
- Up to 60% stronger than comparable leading nitrile brands

EN 374



EN 374



Item No.	Product
ANS93-833-S	Gloves nitrile thin microflex blue small 250pcs
ANS93-833-M	Gloves nitrile thin microflex blue medium 250pcs
ANS93-833-L	Gloves nitrile thin microflex blue large 250pcs
ANS93-833-XL	Gloves nitrile thin microflex blue x-large 250pcs

Microflex® 93-852

Distinct black nitrile exam gloves



For use when dark colours are needed

- The distinct colour of the Microflex® 93-852 hides stains and provides a contrasting backdrop for identifying lighter coloured materials
- The fully textured design and non-foaming formula delivers a firm and consistent grip
- Protects against Type I allergies
- Offers a higher tensile strength compared to EN 455 standards, allowing your hands to move freely and comfortably

EN 374



EN 374



Item No.	Product
ANS93-852-XS	Gloves nitrile Micro-Flex black x-small 100pcs
ANS93-852-S	Gloves nitrile Micro-Flex black small 100pcs
ANS93-852-M	Gloves nitrile Micro-Flex black medium 100pcs
ANS93-852-L	Gloves nitrile Micro-Flex black large 100pcs
ANS93-852-XL	Gloves nitrile Micro-Flex black x-large 100pcs

TouchNTuff® 92-600

Proven splash resistance against hazardous chemicals



For general lab use where additional protection is needed

- Outstanding resistance to a greater variety of industrial chemicals for longer periods than any other nitrile disposable gloves
- Up to four times the puncture resistance of comparable natural rubber latex, and three times the resistance of similar neoprene gloves
- With a unique “Thin Nitrile Technology” formulation, this glove offers easy donning and strong grip in wet or dry conditions
- No natural rubber proteins, which means no risk of Type I allergies to latex for the wearer

EN 374



EN 374



Item No.	Product
ANS92-600-S	Gloves Touch N Tuff small nitrile 100pcs
ANS92-600-M	Gloves Touch N Tuff medium nitrile 100pcs
ANS92-600-L	Gloves Touch N Tuff large nitrile 100pcs
ANS92-600-XL	Gloves Touch N Tuff x-large nitrile 100pcs

Microflex[®] 93-843

Durable, heavy-duty coverage nitrile gloves



For lab use when high levels of confidence are required in demanding applications

- Advanced barrier protection with 0.65 AQL pinhole level
- Provides sturdy coverage for demanding applications
- Effortless donning and doffing with a polymer coating
- Resistant to tape and adhesives due to non-stock properties built into the glove formulation



Item No.	Product
ANS93-843-XS	Gloves nitrile microflex violet extra small 100pcs
ANS93-843-S	Gloves nitrile microflex violet small 100pcs
ANS93-843-M	Gloves nitrile microflex violet medium 100pcs
ANS93-843-L	Gloves nitrile microflex violet large 100pcs
ANS93-843-XL	Gloves nitrile microflex violet extra large 100pcs

Microflex® 93-853

High risk nitrile gloves



For lab use when high levels of confidence are required in demanding applications, especially when handling cytotoxic materials

- Approved for use with cytotoxic drugs
- Extended cuff for additional protection
- Up to three times the puncture resistance of latex or vinyl gloves
- Pinhole rate of 0.65 AQL
- Resistant to tape and adhesives due to non-stock properties built into the glove formulation
- Textured fingers ensure strong, efficient grip and excellent worker protection

EN 374



EN 374



Item No.	Product
ANS93-853-XS	Gloves nitrile Micro-Flex blue extra small 50pcs
ANS93-853-S	Gloves nitrile Micro-Flex blue small 50pcs
ANS93-853-M	Gloves nitrile Micro-Flex blue medium 50pcs
ANS93-853-L	Gloves nitrile Micro-Flex blue large 50pcs
ANS93-853-XL	Gloves nitrile Micro-Flex blue x-large 50pcs

Microflex® 93-260

Thinnest chemical resistant synthetic composite glove



For use when extended chemical protection is required without sacrificing dexterity

- Superior chemical protection
- Triple layered nitrile + neoprene design to give superior protection against harsh chemicals
- Pinhole level of 0.65 AQL
- Extra long cuff for added protection to wrist and forearm
- Unparalleled comfort
- Thin construction provides a high level of tactility in comparison to re-usable gloves
- Extra soft material for flexibility and feel for long periods of use

EN 374



JKL

EN 374



EN 374



Item No.	Product
ANS93-260-XS	Gloves Nitrile + neoprene microflex x-small 50pcs
ANS93-260-S	Gloves Nitrile + neoprene microflex small 50pcs
ANS93-260-M	Gloves Nitrile + neoprene microflex medium 50pcs
ANS93-260-L	Gloves Nitrile + neoprene microflex large 50pcs
ANS93-260-XL	Gloves Nitrile + neoprene microflex x-large 50pcs

Barrier[®] 02-100

Laminated film re-usable glove



For extreme chemical resistance

- HPPE laminated film gives extreme resistance to a wide range of chemicals
- Proprietary seam-fusion technology provides a secure seal against chemicals
- Wing-thumb, hand-specific design provides greater dexterity and reduced hand fatigue
- Comfortable to wear, even for extended periods
- Can be worn as a liner under heavier gloves

EN 374



ABC

EN 374



EN 374



Item No.	Product
ANS2-100-8	Gloves Barrier size 8 flat film 12 pairs
ANS2-100-9	Gloves Barrier size 9 flat film 12 pairs
ANS2-100-10	Gloves Barrier size 10 flat film 12 pairs



Ansell

Find out more at [thermofisher.com.au](https://www.thermofisher.com.au)

For Research Use Only. Not for use in diagnostic procedures. © 2017 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated on [thermofisher.com.au/trademarks](https://www.thermofisher.com.au/trademarks). 1487632307

Order Placement:

For customer service, call 1300-735-292

To fax an order, use 1800-067-639

To email an order, ordersau@thermofisher.com

Contact Us:

For customer service, call 1300-735-292

For service and calibration, call 1300-736-767

To order online: [thermofisher.com.au](https://www.thermofisher.com.au)

ThermoFisher
SCIENTIFIC