

Item Number	Item Description
10010015	PBS PH7.4 W/O CAMG USA PLASTIC
10010023	PBS 7.4 1X
10010049	PBS 7.4 1X
10010056	PBS PH7.4 W/O CAMG USA PLASTIC
10370047	MEM EARLES (CE)
10370070	MEM
10565042	DMEM F12
10938025	DMEM (HIGH GLUCOSE) W/O L-GLUT
10938026	DMEM (HIGH GLUCOSE) W/O L-GLUT
11120001	MEM VITAMINS (100X)
11120037	MEM VITAMINS (100X)
11120061	MEM VITAMINS (100X)
11120062	MEM VITAMINS (100X)
11130036	AMINO ACIDS W/O GLUT (50X)(CE)
11130077	MEM AMINO ACIDS W/O GLUT (50X)
11140035	NON ESS AMINO ACIDS (100X)(CE)
11140068	MEM NON ESS AMINO ACIDS (100X)
11269016	AMNIOMAX II COMPLETE
11320074	D-MEM/F:12(1:1)(CE)
11320084	DULBECCO'S MEM/NUT MIX F-12
11330032	DMEM NUTRIENT MIX F12
11330057	DMEM NUTRIENT MIX F12
11415049	L-15 (LEIBOVITZ) MEDIUM (CE)
11415056	L-15 (LEIBOVITZ) MEDIUM
11835063	RPMI 1640 (1X) W/O PH RED (CE)
11835105	RPMI 1640 (1X) LIQUID
11875085	RPMI 1640
11875093	RPMI 1640
11875119	RPMI 1640
11875135	RPMI 1640
11880028	DMEM W/O PR W/O L-GLUT
11880036	DMEM W/O PR W/O L-GLUT
14025050	HBSS, W/O PHENOL RED (1X) (CE)
14025100	HBSS, W/O PHENOL RED (1X)
14040083	PBS,DULB (1X)+CA,+MG (CE)
14040091	PBS,DULB (1X)+CA,+MG (CE)
14040117	DPBS
14040166	PBS,DULB(1X)+CA,+MG (CE)
14040174	PBS,DULB (1X)+CA,+MG (CE)
14040224	PBS,DULB (1X)+CA,+MG (CE)
14060040	HBSS, HANK'S (10X) (CE)
14060073	HBSS (10X)
14065049	HBSS,W/O PHENOL RED (10X)(CE)
14065072	HBSS,W/O PHENOL RED (10X)
14080048	PBS, DULBECCO'S (10X) (CE)
14080089	PBS, DULBECCO'S (10X)
14155046	EBSS,W/O CA,MG AND PH RED (CE)
14155048	EBSS,W/O CA,MG AND PH RED (CE)
14170070	HBSS,W/O CA AND MG (1X) (CE)
14170088	HBSS,W/O CA AND MG (1X) (CE)

14170138	HBSS,W/O CA AND MG (1X)
14170146	HBSS,W/O CA AND MG (1X)
14175046	HBSS,W/O CA,MG,PH RED (1X)(CE)
14175053	HBSS,W/O CA,MG,PH RED (1X)(CE)
14175129	HBSS,W/O CA,MG AND PH RED (1X)
14175137	HBSS,W/O CA,MG AND PH RED (1X)
14180046	HBSS,W/O CA AND MG (10X) (CE)
14180080	HBSS,W/O CA AND MG (10X) (CE)
14185045	HBSS,W/O CA,MG,PH RED(10X)(CE)
14185087	HBSS,W/O CA,MG,PH RED(10X)(CE)
14190086	PBS,D'BECCOS W/O CA,MG(1X)(CE)
14190094	PBS,D'BECCOS W/O CA,MG(1X)(CE)
14190136	DPBS
14190144	DPBS
14190169	PBS DULBECCO'S W/O CA MG (1X)
14190185	PBS,DULBECCOS W/O CA,MG (1X)
14190230	PBS, D'BECCOS W/O CA, MG (1X)
14190240	PBS DULBECCOS W/O CA,MG(1X)
14190250	DPBS
14190326	DPBS
14190342	DPBS
14190367	DPBS
14200059	PBS,D'BECCOS W/OCA,MG(10X)(CE)
14200067	PBS,D'BECCOS W/OCA,MG(10X)(CE)
14200083	PBS, DULBECCOS W/O CA,MG (10X)
14200091	PBS, DULBECCOS W/O CA,MG (10X)
15630049	HEPES BUFFER 1M (CE)
15630056	HEPES BUFFER 1M (CE)
15630122	HEPES BUFFER 1M
17001074	AMNIOMAX C100 BASAL MED
17001094	AMNIOMAX C100 BASAL MED
20012019	PBS, PH 7.2
20012068	PBS, PH 7.2
21063029	DMEM
21063045	DMEM
21090022	MEM-EARLES W/O L-GLUT (CE)
21090055	MEM-EARLES W/O L-GLUT
21157029	MEDIUM 199 W/O PH RED (2X)
21157030	MEDIUM 199 W/O PH RED (2X)
21180021	MEDIUM 199 EARLES (10X) P
21180022	MEDIUM 199 EARLES (10X)
21331020	DMEM/F12 (1:1) W/O L-GLUT (CE)
21331046	DMEM/F12 (1:1) W/O L-GLUT
21430020	MEM-EARLES W/O L-GLUT(10X)(CE)
21430079	MEM (10X)
21575022	MEM-HANKS W/L-GLUT (CE)
21575097	MEM-HANKS W/L-GLUT
21875034	RPMI MEDIUM 1640 (CE)
21875042	RPMI MEDIUM 1640 (CE)
21875059	RPMI 1640 W/GLUT (1X) (CE)
21875091	RPMI MEDIUM 1640
21875109	RPMI MEDIUM 1640

21875158	RPMI 1640 W/GLUT (1X)
21885025	DMEM W/GLUTAMAX-I PYR,IG/L, GLU
21885108	DMEM W/GLUTAMAX-I PYR,IG/L, GLU
21935028	MOD EAGLE MEDW/O PH RED(2X)CE
21935029	MOD EAGLE MEDW/O PH RED(2X)CE
22320022	D-MEM(LG)W/NA PYR & HEPES (CE)
22320030	DULBECCO'S W/NA PYR & HEPES
22350029	MEDIUM 199 HANKS & HEPES (CE)
22350078	MEDIUM 199 HANKS & HEPES
22561021	MEM ALPHA W/O NUCLEOSIDES
22561054	MEM ALPHA W/O NUCLEOSIDES
22571020	MEM ALPHA W/NUCLEOSIDES (CE)
22571038	MEM ALPHA W/NUCLEOSIDES
24020083	HBSS, HANKS' (1X) (CE)
24020091	HBSS, HANKS' (1X) (CE)
24020133	HBSS, HANKS' (1X)
24020141	HBSS, HANKS' (1X)
31095029	MEM-EARLES & L-GLUT (CE)
31095052	MEM-EARLES & L-GLUT
31150022	MEDIUM 199 EARLES SALTS (CE)
31150030	MEDIUM 199 EARLES SALTS
31153026	MEDIUM 199 EARLES MOD SALTS
31153027	MEDIUM 199 EARLES MOD SALTS
31330038	DMEM:F12(1:1) W/HEPES (CE)
31330095	DMEM/F12 (1:1) W/15MM HEPE UKP
31331028	DMEM/NUT.MIX F-12 W/GLUT-I
31331093	DMEM/NUT.MIX F-12 W/GLUT-I
31415029	L-15 LEIBOVITZ W/GLUTAMAX-I
31415086	L-15 LEIBOVITZ W/GLUTAMAX-I
31870017	RPMI-1640 W/O L-GLUTAMINE (CE)
31870025	RPMI-1640 W/O L-GLUTAMINE (CE)
31870074	RPMI-1640 W/O L-GLUTAMINE
31870082	RPMI-1640 W/O L-GLUTAMINE
31885023	D-MEM (LG)W/NA PYR.(CE)
31885049	DULBECCO'S MED W/NA PYR.
31966021	DMEM W/GLUTAMAX-I,PYR,4.5G GLU
31966047	DMEM W/GLUTAMAX-I,PYR,4.5G GLU
32360026	MEM-EARLES HEPES W/OL-GLUT(CE)
32360034	MEM-EARLES HEPES W/O L-GLUT
32404014	RPMI 1640 W/O PHENOL RED
32404015	RPMI 1640 W/O PHENOL RED
32430027	DMEM W/GLUT-I,HEPES,W/O PYR
32430100	DMEM W/GLUT-I,HEPES,W/O PYR
32561029	MEM ALPHA W/O RIBOS W/GLUMAX-I
32561094	MEM ALPHA W/O RIBOS W/GLUMAX-I
32571028	MEM ALPHA W/RIBOS W/GLUTAMAX-I
32571093	MEM ALPHA W/RIBOS W/GLUTAMAX-I
41010026	BME,EARLES W/O L-GLUT (CE)
41010109	BME,EARLES W/O L-GLUT
41090028	MEM W/GLUTAMAX-I,EARLES
41090093	MEM W/GLUTAMAX-I,EARLES
41150020	MEDIUM 199 W/GLUTAMAX-I EARLES

41150087	MEDIUM 199 W/GLUTAMAX-I EARLES
41965039	D-MEM (HG) W/O NA PYR (CE)
41965047	DMEM (HG) W/O NA PYR (1X)(CE)
41965062	DULBECCO'S MED W/O NA PYR
41965120	DMEM (HG) W/O NA PYR (1X)
41966029	D-MEM (HG) W/NA PYR (CE)
41966052	DULB MED WITH 0.11G/L NA PYR
41966161	D-MEM (HG) W/NA PYR (CE)
42360024	MEM W/GLUTAMAX-I,EARLES,HEPES
42360081	MEM W/GLUTAMAX-I,EARLES,HEPES
42401018	RPMI1640 W/25MMHEPES W/OL-GLUT
42401042	RPMI1640 W/25MMHEPES W/OL-GLUT
42402016	RPMI1640 W/20MMHEPES W/OL-GLUT
42402017	RPMI-1640 WITH 20MM HEPES
42430025	D-MEM (HG)W/O PYR W/HEPES (CE)
42430082	DULBECCO'S W/O NA PYR W/HEPES
51200046	MEM EARLES (CE)
51200087	MINIMAL ESSENTIAL MEDIUM 1X
52400017	RPMI MEDIUM 1640 W/HEPES (CE)
52400025	RPMI MEDIUM 1640 W/HEPES (CE)
52400041	RPMI MEDIUM 1640 W/HEPES
52400058	RPMI MEDIUM 1640 W/HEPES
61870010	RPMI 1640 W/GLUTAMAX-I
61870044	RPMI 1640 W/GLUTAMAX-I
61965026	DMEM HIGH W/GLUTAMAX - I
61965059	DMEM HIGH W/GLUTAMAX - I
61965240	DMEM HIGH W/GLUTAMAX-1
70011036	PBS PH7.4 W/O CAMG USA PLASTIC
70011051	PBS PH7.4 W/O CAMG USA PLASTIC
70013016	10X PBS PH7.2 W/O CAMG USA
70013065	10X PBS PH7.2 W/O CAMG USA
72400013	RPMI 1640 W/HEPES W/GLUTAMAX-I
72400021	RPMI 1640 W/HEPES W/GLUTAMAX-I
72400054	RPMI 1640 W/HEPES W/GLUTAMAX-I
72400112	RPMI 1640 MEDIUM