

Part Number	Part Description	Liquid/ Powder
10012011	MEDIUM199 HANKSW/25MM HEPE(CE)	Powder
10012037	MEDIUM199 HANKSW/25MM HEPE(CE)	Powder
11058021	OPTI MEM I	Liquid
11058021	OPTI MEM I	Liquid
11058022	OPTI MEM I	Liquid
11220035	WAYMOUTHS MB 752 1 MED	Liquid
11220098	WAYMOUTHS MB 752 1 MED	Liquid
11360039	SODIUM PYRUVATE MEM 100MM(CE)	Liquid
11360070	SODIUM PYRUVATE SOL	Liquid
11360097	SODIUM PYRUVATE SOL	Liquid
11700077	MEM EARLES	Powder
11700077	MEM EARLES	Powder
11900016	MEM ALPHA W/NUCLEOSIDES	Powder
11900024	MEM ALPHA	Powder
11900073	MEM ALPHA	Powder
11900073	MEM ALPHA	Powder
12000014	MEM ALPHA W/O NUCLEOSIDES	Powder
12000022	MEM ALPHA	Powder
12000063	MEM ALPHA	Powder
12000063	MEM ALPHA	Powder
12100046	DMEM	Powder
12100061	DMEM	Powder
12200036	IMDM	Powder
12200069	IMDM	Powder
12400024	DMEM NUTRIENT MIX F12	Powder
12500062	DMEM NUTRIENT MIX F12	Powder
12500096	DMEM NUTRIENT MIX F12	Powder
12551032	WILLIAMS MED E	Liquid
12551098	WILLIAMS MED E	Liquid
12591038	BGJB MED	Liquid
12591098	BGJB MED	Liquid
12800017	DMEM	Powder
12800082	DMEM	Powder
13018015	RPMI 1640 W/25MM HEPES (CE)	Powder
13018031	RPMI 1640 W/25MM HEPES (CE)	Powder
21300017	P.B.S. (DULBECCO'S)	Powder
21300025	DPBS	Powder
21300058	DPBS	Powder
21300058	DPBS	Powder
21300074	DPBS	Powder
21600010	DPBS	Powder
21600044	DPBS	Powder
21600069	DPBS	Powder
21700018	F 12 NUTRIENT MIX, HAMS	Powder

21700018	F 12 NUTRIENT MIX, HAMS	Powder
21700026	NUTRIENT MIXTURE F-12 (HAM)	Powder
21700075	F 12 NUTRIENT MIX, HAMS	Powder
22100093	GMEM	Powder
22551022	WILLIAMS' MEDIUM E (CE)	Liquid
22600050	OPTI MEM I	Powder
22600134	OPTI MEM I	Powder
22600134	OPTI MEM I	Powder
23400021	RPMI 1640	Powder
23400062	RPMI 1640	Powder
31100019	MED 199 EARLES	Powder
31100019	MED 199 EARLES	Powder
31100027	MEDIUM 199 W/EBSS	Powder
31100035	MED 199 EARLES	Powder
31220023	WAYMOUTH MEDIUM MB 752/1 (CE)	Liquid
31600034	DMEM	Powder
31600083	DMEM	Powder
31600083	DMEM	Powder
31600091	DMEM	Powder
31600091	DMEM	Powder
31800022	RPMI 1640	Powder
31800089	RPMI 1640	Powder
31800105	RPMI 1640	Powder
31985047	OPTIMEM 1 (CE)	Liquid
31985062	OPTI MEM I	Liquid
31985070	OPTI MEM I	Liquid
31985088	OPTI MEM I	Liquid
31985097	OPTI MEM I	Liquid
32500035	DMEM/F12 (1:1) W/L-GLUT (CE)	Powder
32500043	DMEM/F12 (1:1) W/L-GLUT (CE)	Powder
32500050	DMEM/F12 (1:1) W/L-GLUT	Powder
32551020	WILLIAMS E W/GLUTAMAX-I	Liquid
41300021	LEIBOVITZ'S L-15 MEDIUM	Powder
41300039	LEIBOVITZ L 15 MED	Powder
41300070	LEIBOVITZ L 15 MED	Powder
41300070	LEIBOVITZ L 15 MED	Powder
41500018	MEM EARLES NEAA	Powder
41500018	MEM EARLES NEAA	Powder
41500034	MEM EARLES NEAA	Powder
41500067	MEM W/EBSS W/NEAA	Powder
41500083	MEM EARLES NEAA	Powder
41500083	MEM EARLES NEAA	Powder
42200014	ISCOVE MOD.DULBECCO (IMDM)(CE)	Powder
42200030	ISCOVE MOD.DULBECCO (IMDM)(CE)	Powder
42400010	DUL MEM/NUTMIX F12 W/HEPES(CE)	Powder
42400028	DUL MEM/NUTMIX F12 W/HEPES(CE)	Powder
51800019	RPMI-1640 MEDIUM (CE)	Powder

51800035	RPMI-1640 MEDIUM (CE)	Powder
51800043	RPMI-1640 MEDIUM (CE)	Powder
51985026	OPTIMEM-I W/GLUTAMAX-I (CE)	Liquid
51985034	OPTI MEM I W/GLUTAMAX-I	Liquid
51985091	OPTI MEM I W/GLUTAMAX-I	Liquid
61100053	MEM W/EBSS	Powder
61100061	MEM EARLES	Powder
61100087	MEM EARLES	Powder
61100087	MEM EARLES	Powder
61100103	MEM EARLES	Powder
61100103	MEM EARLES	Powder
11012044	MEM W/HBSS W/25MM HEPES	Powder
52100021	D-MEM (HG) W/O PYRUVATE (CE)	Powder
52100039	D-MEM (HG) W/O PYRUVATE (CE)	Powder
52100047	D-MEM (HG) W/O PYRUVATE (CE)	Powder
21530027	CMRL-1066 W/O L-GLUT (CE)	Liquid
21710025	BHK-21(GLASGOW MEM)W/O TPB(CE)	Liquid
21765029	NUTRIENT MIXTURE F-12(HAM)(CE)	Liquid
21980032	ISCOVES MOD.DULBECCO(IMDM)(CE)	Liquid
22330021	MCCOYS 5A W/HEPES W/O SERUM CE	Liquid
22340020	MEDIUM 199 EARLES & HEPES (CE)	Liquid
22390017	NUTRIENT MIX F-10 W/HEPES (CE)	Liquid
22390025	NUTRIENT MIX F-10 W/HEPES (CE)	Liquid
25030024	L-GLUTAMINE 200MM	Liquid
25030032	L GLUTAMINE, 100X	Liquid
26600023	MCCOY'S 5A W/O SERUM (CE)	Liquid
31550015	NUTRIENT MIX F-10 (HAM)(CE)	Liquid
31550023	NUTRIENT MIX F-10 (HAM) (CE)	Liquid
31765027	NUT MIX F-12 W/GLUTAMAX-I	Liquid
31980022	ISCOVES W/GLUTAMAX-I	Liquid
35050038	GLUTAMAX 1 (100X) (CE)	Liquid
36600021	MCCOYS 5A W/GLUTAMAX I	Liquid
41550021	NUT MIX F-10 W/GLUTAMAX-I	Liquid
25030081	L GLUTAMINE, 100X	Liquid
10575090	POTASSIUM CHLORIDE 0.075M	Liquid
11150059	Medium 199, Earle's Salts	Liquid
11380098	SMEM	Liquid
11530037	CMRL 1066	Liquid
11530098	CMRL 1066	Liquid
11550043	F 10 NUTRIENT MIX, HAMS	Liquid
11550098	F 10 NUTRIENT MIX, HAMS	Liquid
11710035	GMEM	Liquid
11710098	GMEM	Liquid
11765047	F 12 NUTRIENT MIX, HAMS	Liquid
11765054	F 12 NUTRIENT MIX, HAMS	Liquid
11765062	F 12 NUTRIENT MIX, HAMS	Liquid
11765070	F 12 NUTRIENT MIX, HAMS	Liquid

11825015	10X MEDIUM 199 W/O GLUTAMINE	Liquid
11825098	10X MEDIUM 199 W/O GLUTAMINE	Liquid
11935046	MOD EAGLE MED, 2X	Liquid
11935098	MOD EAGLE MED, 2X	Liquid
12330031	MCCOYS 5A MED MOD	Liquid
12330098	MCCOYS 5A MED MOD	Liquid
12340030	MED 199 EARLES	Liquid
12340098	MED 199 EARLES	Liquid
12350039	MED 199 HANKS	Liquid
12350098	MED 199 HANKS	Liquid
12390035	F 10 NUTRIENT MIX, HAMS	Liquid
12390098	F 10 NUTRIENT MIX, HAMS	Liquid
12440053	IMDM	Liquid
12440061	IMDM	Liquid
12440079	IMDM	Liquid
16600082	MCCOYS 5A MED MOD	Liquid
16600108	MCCOYS 5A MED MOD	Liquid
21010046	BME EARLES	Liquid
21010098	BME EARLES	Liquid
21340039	NCTC 109	Liquid
21340047	NCTC 109	Liquid
21340098	NCTC 109	Liquid
25030081	L GLUTAMINE, 100X	Liquid
25030149	L GLUTAMINE, 100X	Liquid
25030164	L GLUTAMINE, 100X	Liquid
21340039	NCTC 109	Liquid
3110027	MEDIUM 199 EARLES SALTS	Liquid
31150030	MEDIUM 199 EARLES SALTS	Liquid
31765035	F 12 NUTRIENT MIX, HAMS	Liquid
31765092	F 12 NUTRIENT MIX, HAMS	Liquid
31980030	IMDM	Liquid
31980097	IMDM	Liquid
35050061	GLUTAMAX I, 100X	Liquid
35050079	GLUTAMAX I, 100X	Liquid