

Toxicology

## Indiko Plus clinical chemistry analyzer

Fast and accurate results using high-quality reagents for drugs of abuse testing



### Fast and accurate benchtop

Minimal hands-on time



### Cost-effective and reliable

Continuous access, self-contained, auto-dilution & reruns, bidirectional LIS connection



### Easy to use

Intuitive software interface and comprehensive testing menu



Indiko Plus Chemistry Analyzer

Up to 200 test/hr

## High-quality reagents

For all types of platforms and matrices - serum, urine, oral fluids

Toxicology reagents
Amphetamine (Ecstasy)
Amphetamine (Methamphetamine)
Barbiturate
Benzodiazepine
Buprenorphine
Buprenorphine II
Cannabinoid (THC)
Cocaine
Cotinine
Ecstasy
Ecstasy Plus
Ethyl Alcohol
Ethyl Glucuronide EtG (CJ&F)
Fentanyl (CJ&F)
Fentanyl II (FDA Approved)
Heroin Metabolite (6-Acetylmorphine)
Hydrocodone
Methadone
Methadone Metabolite
Methaqualone
Mitragynine (Kratom) (CJ&F)
Opiate
Oxycodone
Phencyclidine (PCP)
Propoxyphene (PPX)
Synthetic Cannabinoid - AB PINACA (CJ&F)
Synthetic Cannabinoid - UR-144 (CJ&F)

### CEDIA™ drugs of abuse assays

Valued worldwide for their accurate, precision, consistency and longer shelf life

### DRI™ drugs of abuse assays

Liquid, ready-to-use reagents offer analytical accuracy while eliminating reagent preparation steps

Serum tests
Serum, Acetaminophen
Serum, Barbiturate
Serum, Benzodiazepine
Serum, Tricyclics

Specimen validity tests
DRI Creatinine-Detect
DRI General Oxidant-Detect
DRI Gravity-Detect
DRI pH-Detect



## SAMHSA qualified

### SAMHSA “9”

Thermo Fisher Scientific assay	Analytes	Cutoff ng/mL	Cross-reactivity
DRI Amphetamine	Amphetamine	500	100%
	Methamphetamine		100%
DRI THC	THC (11-nor- $\Delta^9$ -THC-COOH)	50	100%
DRI Cocaine	Cocaine metabolite (Benzoylecgonine)	150	100%
DRI Opiate	Morphine	2000	100%
	Codeine		210%
DRI Phencyclidine (PCP)	Phencyclidine (PCP)	25	100%
CEDIA™ Heroin Metabolite (6-AM)	6-Acetylmorphine (6-AM)	10	100%
DRI Ecstasy Plus	MDMA	500	100%
	MDA		80%
DRI Hydrocodone	Hydrocodone	300	102%
	Hydromorphone		97%
DRI Oxycodone	Oxycodone	100	100%
	Oxymorphone		103%

### Thermo Scientific specimen validity tests

DRI Creatinine-Detect

DRI Gravity-Detect

DRI pH-Detect

DRI General Oxidant-Detect



## Training, education, service and support

Experienced field service team and toll free technical support hotline available to you 24/7.

Learn more at [thermofisher.com/automateddrugscreen](https://thermofisher.com/automateddrugscreen)

**thermo** scientific