

Catalog No.	Product Description	CE Marked	Method	Size	Liquid	Powder	Stability
TR85056	Infinity® ACE (Angiotensin Converting Enzyme)	No	Kinetic	2 x 28 mL	X		Stable Liquid
TR27010	Acid Phosphatase (3-Part Reagents)	Yes	Kinetic	18 x 10 mL		X	5 Days Reconstituted
TR36026	Albumin - Bromocresol Green	Yes	Endpoint	2 x 250 mL	X		Stable Liquid
TR11320	Alkaline Phosphatase (2-Part Reagents)	Yes	Rate/Kinetic	1 x 125 mL	X		Stable Liquid
TR11115	Alkaline Phosphatase (2-Part Reagents)	Yes	Rate/Kinetic	20 x 20 mL		X	30 Days Reconstituted
TR71121	Infinity ALT/GPT	Yes	Kinetic UV	2 x 125 mL	X		Stable Liquid
TR18503	ALT/GPT	Yes	Kinetic UV	10 x 50 mL		X	50 Days Reconstituted
TR60101	Ammonia	Yes	Kinetic	2 x 28 mL	X		Stable Liquid
TR25421	Infinity Amylase EPS	Yes	Kinetic	2 x 125 mL	X		Stable Liquid
TR25115	Amylase EPS	Yes	Kinetic	20 x 20 mL		X	3 Months Reconstituted
TR70121	Infinity AST/GOT	Yes	Kinetic UV	2 x 125 mL	X		Stable Liquid
TR17503	AST/GOT	Yes	Kinetic UV	10 x 50 mL		X	30 Days Reconstituted
TR33321	Direct Bilirubin (Acid Diazo)	Yes	Endpoint	2 x 125 mL	X		21 Days (Working)
1245-250	Total Bilirubin (Diazonium Salt)	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR32321	Total Bilirubin (Acid Diazo)	Yes	Endpoint	2 x 125 mL	X		21 Days (Working)
TR12421	Infinity BUN	Yes	Fixed Rate	2 x 125 mL	X		Stable Liquid
TR12498	Infinity BUN	Yes	Fixed Rate	2 x 500 mL	X		Stable Liquid
TR12003	BUN	Yes	Fixed Rate	10 x 50 mL		X	3 Months Reconstituted
1265-250	Infinity Calcium Arsenazo III	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR29226	Calcium Arsenazo III	No	Endpoint	2 x 250 mL	X		Stable Liquid
TR28321	Infinity Carbon Dioxide	Yes	Enzymatic Endpoint	2 x 125 mL	X		Stable Liquid
TR38026	Chloride	No	Endpoint	2 x 250 mL	X		Stable Liquid
TR13421	Infinity Total Cholesterol	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR13303	Total Cholesterol	Yes	Endpoint	10 x 50 mL		X	3 Months Reconstituted
TR39601	HDL Cholesterol/Automated (2-Part Reagents)	Yes	Endpoint	2 x 30 mL	X		Stable Liquid
TR39602	HDL Cholesterol/Automated (2-Part Reagents)	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
1335-500	HDL Cholesterol PPT Reagents	Yes	Precipitation	2 x 250 mL	X		Stable Liquid
TR53202	LDL Cholesterol/Automated (2-Part Reagents)	No	Endpoint	2 x 30 mL	X		Stable Liquid
TR55017	Cholinesterase	Yes	Kinetic	20 x 7 mL		X	3 Days Reconstituted
TR14010	CK-NAC	No	Kinetic	20 x 10 mL		X	7 Days Reconstituted
TR14115	CK-NAC	Yes	Kinetic	20 x 20 mL		X	7 Days Reconstituted
TR14314	CK-MB (2-Part Reagents) (Not for sale in the U.S.)	Yes	Kinetic	20 x 5 mL		X	7 Days Reconstituted
TR61001	Copper (2-Part Reagents)	Yes	Endpoint	1 x 50 mL	X		5 Days (Working)
TR35401	Enzymatic Creatinine (2-Part Reagents)	No	Endpoint	2 x 30 mL	X		Stable Liquid
TR35121	Infinity Creatinine (Modified Jaffe)	Yes	Rate	2 x 125 mL	X		Stable Liquid
TR19110	GGT	Yes	Kinetic	20 x 10 mL		X	21 Days Reconstituted
TR19320	GGT (2-Part Reagents)	Yes	Kinetic	1 x 125 mL	X		Stable Liquid
TR15421	Infinity Glucose Hexokinase	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR15498	Infinity Glucose Hexokinase	Yes	Endpoint	2 x 500 mL	X		Stable Liquid
TR15003	Glucose Hexokinase	Yes	Endpoint	10 x 50 mL		X	30 Days Reconstituted
TR15221	Infinity Glucose Oxidase	Yes	Endpoint	10 x 50 mL	X		Stable Liquid
TR15103	Glucose Oxidase	Yes	Endpoint	10 x 50 mL		X	90 Days Reconstituted
TS3500	Direct TIBC	No	Endpoint	2 x 60 ml & 2x30 ml	X		Stable Liquid
1580-300	Iron/Ferene (3-Part Reagents)	Yes	Endpoint	1 x 250 mL	X		Stable Liquid
TR46101	Iron/Ferrozine (2-Part Reagents)	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR46201	UIBC/Ferrozine (3-Part Reagents)	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
1590-500	Iron/UIBC Set/Ferene (4-Part Reagents)	Yes	Endpoint	1 x 250 mL & 1 x 200 mL	X		Stable Liquid
TR20010	LDH-L	Yes	Kinetic	20 x 10 mL		X	5 Days Reconstituted

TR20015	LDH-L	Yes	Kinetic	20 x 20 mL		X	5 Days Reconstituted
7500-120A/220A	LDH-L (2-Part Reagents)	Yes	Kinetic	4 x 500 mL	X		Stable Liquid
<b>Catalog No.</b>	<b>Product Description</b>	<b>CE Marked</b>	<b>Method</b>	<b>Size</b>	<b>Liquid</b>	<b>Powder</b>	<b>Stability</b>
TR66056	Infinity Lithium	Yes	Endpoint	2 x 28 mL	X		Stable Liquid
TR31126	Infinity Magnesium/Arsenazo	Yes	Endpoint	2 x 250 mL	X		Stable Liquid
TR52001	PBG (Porphobilinogen)	Yes	Anion Exchange	10 Tests		X	12 Months Reconstituted
TR30026	Phosphorus UV	Yes	Endpoint	2 x 250 mL	X		Stable Liquid
TR34026	Total Protein	Yes	Endpoint	2 x 250 mL	X		Stable Liquid
1715-250	Microprotein - Pyrogallol Red	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR50001	Microprotein - Benzethonium Chloride (2-Part Rgts)	Yes	Turbidimetric	1 x 125 mL	X		Stable Liquid
TR22421	Infinity Triglycerides	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR22203	Triglycerides	Yes	Endpoint	10 x 50 mL		X	3 Months Reconstituted
TR24321	Infinity Uric Acid	Yes	Endpoint	2 x 125 mL	X		Stable Liquid
TR24003	Uric Acid	Yes	Endpoint	10 x 50 mL		X	3 Months Reconstituted

Applications available for most Clinical Chemistry Analyzers

For details, contact Thermo Fisher Scientific Technical Support at

1-800-528-0494, Option 2

[techsupport.diagnostics.mtn@thermofisher.com](mailto:techsupport.diagnostics.mtn@thermofisher.com)