

Manufacturer	Model	Plate	Deepwell Plate Height Limit *
Agilent	1100 Well-Plate G1367A	2	45mm
Agilent	1200 Well-plate G1377A	2	45mm
Agilent	1260 Infinity High Performance G1367E	2	45mm
Agilent	1290 Infinity Autosampler G4226A	2	45mm
Agilent	CTC HTS PAL /CTC HTC PAL/CTC GC PAL	2-4	Standard DW Plate
CTC (LEAP)	HTX PAL/HTC PAL/ HTS PAL	2-4	Standard DW Plate
CTC (LEAP)	Combi PAL/GC PAL	2-4	Standard DW Plate
Gerstel	MPS, MPS2	Custom	Standard DW Plate
Jasco	AS-2059/AS-2059Plus	2	Standard DW Plate
Jasco	AS-2059-SF/X-LC	2	Standard DW Plate
Knauer	Autosampler 3950	2	47mm
Sepiatech	Sepmatix x8	8	Standard DW Plate
Shimadzu	SIL-10AF/SIL-10AP/SIL-10AxL/SIL-10HTA/SIL-10HTC	2	Standard DW Plate
Shimadzu	SIL-HT	4	Standard DW Plate
Shimadzu	SIL-20A/SIL-20AC (Prominence)	2	Standard DW Plate
Shimadzu	SIL-20AXR/SIL-20ACXR (Prominence)	2	Standard DW Plate
Shimadzu	SIL-30AC(Nexera)	2	Standard DW Plate
Spark	Alias	2	47mm
Spark	Endurance	2-4	47mm
Spark	Integrity / IntegrityPlus	2-4	47mm
Spark	Reliance/Symbiosis Pharma	2	Standard DW Plate
Spark	Symbiosis Pico	>10	Standard DW Plate
Thermo Scientific	Accela High Speed LC Autosampler	2	47mm
Thermo Scientific	Accela Open Autosampler	4	Standard DW Plate
Thermo Scientific	AS-AP	2-4	Standard DW Plate
Thermo Scientific	OAS-3300TXRS Autosampler	3	46mm
Thermo Scientific	OAS-3600TXRS Autosampler	3	46mm
Thermo Scientific	TriPlus RSH	3-6	Standard DW Plate
Thermo Scientific	UltiMate WPS-3000TBRS	3	46mm
Thermo Scientific	UltiMate WPS-3000TBSL ANALYTICAL	3	46mm
VWR(Merck®)/Hitachi	LaChrom ULTRA L-2200U	3	46mm
VWR(Merck®)/Hitachi	5210 (Chromaster)	2	Standard DW Plate
Waters	Acquity/Acquity H-Class /Nano Acquity	2	46mm
Waters	Alliance HTS	2	46mm
Waters	Model 2707	Custom	Standard DW Plate
Waters	Model 2767	Custom	Standard DW Plate
Waters	Model 2777	Custom	Standard DW Plate

* Where stated deepwell plate limit is for plate and sealing mat inclusive.