

Cross reference
syringe filter units

	Thermo Scientific Titan3 Product code	Ring color
4 mm syringe filter 0.45 µm nylon	44504-NN	Transparent Green
4 mm syringe filter 0.2 µm polypropylene		N/A
4 mm syringe filter 0.45 µm cellulose acetate		N/A
4 mm syringe filter 0.2 µm cellulose acetate	44502-CA	Light Green
4 mm syringe filter 0.2 µm nylon	42204-NN	Opaque Medium Yellow
4 mm syringe filter 0.45 µm PTFE	44504-NP	Transparent Yellow
4 mm syringe filter 0.2 µm PTFE	42204-NP	Transparent Blue
4 mm syringe filter 0.45 µm PVDF	44504-PV	Red
4 mm syringe filter 0.2 µm PVDF	42204-PV	Black
4 mm syringe filter 0.45 µm regenerated cellulose	54504-RC	Light Brown
4 mm syringe filter 0.2 µm regenerated cellulose	52204-RC	Granite
4 mm syringe filter 0.45 µm polypropylene		N/A
17 mm syringe filter 0.45 µm nylon	44513-NN	Transparent Green
17 mm syringe filter 0.2 µm polypropylene	42213-PP	Royal Blue
17 mm syringe filter 0.45 µm PES for Ion chromatography	44513-PS	Orange/Yellow
17 mm syringe filter 0.45 µm cellulose acetate	44513-CA	Transparent Orange
17 mm syringe filter 0.2 µm cellulose acetate	42213-CA	Light Green
17 mm syringe filter 0.2 µm PES for Ion chromatography	42213-PS	Dark Gray
17 mm syringe filter 0.2 µm nylon	42213-NN	Light Purple
17 mm syringe filter 0.45 µm PTFE	44513-NP	Transparent Yellow
17 mm syringe filter 0.2 µm PTFE	42213-NP	Transparent Blue
17 mm syringe filter 0.45 µm hydrophilic PTFE	44513-NPL	Purple
17 mm syringe filter 0.2 µm hydrophilic PTFE	42213-NPL	Green
17 mm syringe filter 0.45 µm PVDF	44513-PV	Red
17 mm syringe filter 0.2 µm PVDF	42213-PV	Black
17 mm syringe filter 0.45 µm regenerated cellulose	54513-RC	Light Brown
17 mm syringe filter 0.2 µm regenerated cellulose	52213-RC	Granite
17 mm syringe filter 0.45 µm polypropylene	44513-PP	White
30 mm syringe filter 0.45 µm nylon with pre-filter	44525-NN	Transparent Green
30 mm syringe filter 0.2 µm polypropylene	42225-PP	Royal Blue
30 mm syringe filter 5.0 µm PTFE		N/A
30 mm syringe filter 1.25 µm nylon	41225-NN	Opaque Medium Yellow
30 mm syringe filter 1.0 µm PTFE	41025-NP	Dark Blue
30 mm syringe filter 0.45 µm PES for Ion chromatography	44525-PS	Orange/Yellow
30 mm syringe filter 0.45 µm cellulose acetate	44525-CA	Transparent Orange
30 mm syringe filter 0.2 µm cellulose acetate	42225-CA	Light Green
30 mm syringe filter 0.2 µm PES for Ion chromatography with pre-filter	42225-PS	Dark Gray
30 mm syringe filter 0.7 µm glass micro fiber	40725-GM	Amber
30 mm syringe filter 1.2 µm glass micro fiber	41225-GM	Orange
30 mm syringe filter 0.25 µm nylon	45025-NN	Pink
30 mm syringe filter 3.1 µm glass micro fiber	42725-GM	Dark Purple
30 mm syringe filter 0.45 µm PTFE with pre-filter	44525-NP	Transparent Yellow
30 mm syringe filter 0.2 µm PTFE with pre-filter	42225-NP	Transparent Blue
30 mm syringe filter 0.45 µm PVDF	44525-PV	Red
30 mm syringe filter 0.45 µm nylon	44526-NN	White
30 mm syringe filter 0.2 µm PVDF	42225-PV	Black
30 mm syringe filter 0.45 µm regenerated cellulose	54525-RC	Light Brown
30 mm syringe filter 0.2 µm regenerated cellulose	52225-RC	Granite
30 mm syringe filter 0.45 µm polypropylene	44525-PP	White
30 mm syringe filter 0.45 µm nylon	44525-NN	Transparent Green
30 mm syringe filter 0.2 µm nylon	42225-NN	Light Purple
30 mm syringe filter 0.20 µm polypropylene	42225-PP	Royal Blue
30 mm syringe filter 0.45 µm PTFE	44525-NP	Transparent Yellow
30 mm syringe filter 0.45 µm hydrophilic PTFE	44525-NPL	Purple
30 mm syringe filter 0.2 µm hydrophilic PTFE	42225-NPL	Green
30 mm syringe filter 0.45 µm polypropylene	44525-PP	White

Alternative parts are based on a direct technical comparison.

Part number alternatives are based upon closest pack quantity.

Inclusion of parts is no guarantee of identical performance.

GE Healthcare/Whatman GD/X	GE Healthcare/Whatman Puradisc	Spartan	Millipore Millex	PALL Acrodisc	Sartorius Minisart
	6789-0404		SLHNR04NL	4484	
	6788-0402				
	6789-0402		SLGNR04NL		
	6783-0404		SLFHR04NL	4472	17820-K
	6783-0402		SLFGR04NL		17573-K2
	6779-0404		SLHVR04NL		
	6779-0402		SLGVR04NL	4415	
					17822-K
					17821-K
	6788-0404				
6870-1304	6789-1304		SLHN013NL	4426	17762-K
	6788-1302			4567	
	6782-1304				
6880-1304					
6880-1302					
6876-1302	6782-1302				
6870-1302	6789-1302		SLGN013NL	4427	1776B-K
6874-1304	6783-1304		SLFH013NL	4422	17574-K
6874-1302	6783-1302		SLFG013NL	4423	
			SLCRT13NL		
			SLLGH13NK	MS-3301	
6872-1304	6779-1304		SLHV013NL	4457	
6872-1302	6779-1302		SLGV013NL	4455	
					17762-K
					17761-N
6784-1304	6788-1304			4563	
6870-2504	6750-2502	6710-2504	SLHN025NS	4438	1784C-K
6785-2502				4564	
6878-2504	6780-2504	6716-2504	SLHP033NS	4584	
6880-2504					17598-K
6880-2502					17597-K
6878-2502	6780-2502		SLGP033NS		
6890-2507					
6886-2512					
6870-2502	6750-2502		SLGN025NS	4436	1784B-K
6888-2527					
6874-2504	6784-2504	6714-2504	SLFH025NS	4219	17576-K
6874-2502	6784-2502		SLFG025NS	4225	17575-S
6872-2504		6712-2504	SLHV033NS	4408	
6872-2502			SLGV025NB	4406	
					17765-K
					17764-S
		6718-2504		4560	
6870-2504				4549	
6871-2502				4436	1784B-K
6878-2502				4307	
6874-2504				4303	
			SLCR025NB		
			SLLGDZ5NK	MS-3201	
6878-2504				4559	