

Thermo Scientific™ PyGas Analyzer

Recommended Spare Parts

Part Number	Material description
47-1021-0	PCK COALESCER, PACKING
47-1037-0	PCK FILTER ELEMENT, TOP,3inD x 6inL,SS
89-2395-0	COOLING SECTION, SAMPLE CONDITIONER PY-G
53-1001-0	GKT BEVEL SEAT GASKT 1.5in TEF
57-1205-0	INCONEL 625, .035 WIRE C-20 PY-GAS (1 LB
89-2910-0	FILTER SECTION, 2" 300# RF FLANGES
89-2922-0	FILTER SECTION, 2" 150# RF FLANGE, 316SS
89-2934-0	Filter section, C20, 2"150# w/steam
63-1032-0	O-RING, TEFLON, -221 1 7/16 X 1 11/16 X
89-1058-0	ASSEMBLY, FILTER SECTION WITH 1-1/2IN 30
89-1067-0	SECTION, TEMP. MEAS. FOR 3XXX,PY-GAS,304
89-1772-0	ASSY FLTR SECT 5XXX C20 2" 300# FLG
45-1319-0	VALVE, PNEUMATIC N.OPEN FOR UNITED ELECT
89-2373-0	ELBOW, 45 DEGREE W/2IN,300# FLANGES
89-2919-0	FILTER SECTION, 2" 300# RF FLANGES, C20
60-1003-0	NUT 2in HEX NUT,SS
89-1773-0	WLD CLG SECT 5XXX C20 2" 300# FLG
89-1774-0	ASY SC,5XXXA,STEAM I NJECT,C20
45-1318-0	VALVE, PNEUMATIC N.CLOSED FOR UNITED ELE
89-1607-0	ASSEMBLY, TEMP MEAS SECTION W/THERMOWELL
89-2303-0	WLD FS 3XXX 316L 2" 300# TF 2" 150# BF
11-1045-0	ASY FLT SEC 316L 2.5" 300# TF 2" 300# BF
89-1160-0	ASSEMBLY,SAMP COND, COOLING SECTION, 6XX
89-2942-0	Filter section,2" 300#, 2 T-Well w/steam
89-1065-0	WLD CLG SECT 3XXX 304L 1.5" 150# FLG
89-2404-0	WLD CLG SECT 5XXX 347SS 2.5" 300# FLG
89-2627-0	FILTER SECT. ASSY. 316 W/ 2 THERMOWELLS
89-2666-0	TEMP. MEASURE SECT. 7000 SERIES P-G 316L
89-2667-0	ASSY, PY-GAS 7560AS COOLING SECTION, 2in
89-1775-0	ASSEMBLY, TEMP MEAS SECTION W/THERMOWELL
89-1407-0	ASSEMBLY, SC FILTER SECTION, MODEL 6060
89-1408-0	ASSEMBLY,SC,COOLING SECTION, MODEL 6060,
89-1409-0	ASSEMBLY, SC, TEMP MEASURING SECTION MOD
18-1642-0	INDICATOR,TEMP., 0-250,DUAL SCALE, 4IN S
47-1026-0	PCK LOWER PACKING, 6XXX, 316LSS
47-1027-0	PCK UPPER PACKING, 6XXX, 316LSS
89-1726-0	ASSEMBLY, STEAM INJECTION, MOD 346 316L
89-2559-0	FILTER SECTION, 3XXX WITH STEAM INJECTIO
47-1138-0	PCK FILTER PACKING, #24 MESH, C20, 0.003
45-1013-0	VLV AIR OP,2 WAY,NC, .125, 4Tx4M,316
89-2095-0	WLD FLT SECT 3XXX 316L 2" 300# FLG
89-1620-0	ASY TEMP MEASURE SEC T,316LSS
89-2094-0	WLD CLG SECT 3XXX 316L 2" 300# FLG
89-2779-0	TEMP. CONTROL, PYGAS S.S., W/O BULB
89-1657-0	ASY UNION CONN SEAL/ UE P812
45-1015-0	VALVE,PNEU,2W,NC,BRA 1/4in FNPT IN/OUTLE
47-1119-0	PCK FILTER PACKING, #24 MESH, 316SS
89-1786-0	THERMAL ASSEMBLYP812 CONTROLLER,3/32x300
53-1000-0	GASKET, FLANGE, 2 IN 300 LB
53-1015-0	GASKET, 2in, BEVEL SEAT FITTING, TF
47-1368-0	PCK FILTER ELEMENT, TOP PIECE FOR BOTTOM
47-1367-0	PCK FILTER ELEMENT, BOTTOM PIECE FOR PYG
47-1077-0	PCK 1/4in TUBE PACKING, 316LSS