

Centrifuge compatibility for TaqMan Array Cards

Current-generation centrifuges*	Cat. No.		Cat. No.
Megafuge ST4 Plus-MD, 208–240 V, 50/60 Hz	75009503	Sorvall Legend XTR, 120 V (refrigerated)	75004521
Megafuge ST4 Plus, 208–240 V, 50/60 Hz	75009903	Sorvall Legend XTR, 230 V (refrigerated)	75004520
Megafuge ST4 Plus-MD, 120V	75009504	Sorvall Legend XTR, 230 V (US and Canada, refrigerated)	75004523
Megafuge ST4R Plus-MD, 220–240 V, 50 Hz/230 V, 60 Hz	75009518	Sorvall ST 40, 120 V	75004510
Megafuge ST4R Plus, 220 V 60 Hz	75009818	Sorvall ST 40, 230 V	75004509
Megafuge ST4R Plus-MD, 120 V	75009519	Sorvall ST 40R, 120 V (refrigerated)	75004525
Megafuge ST4R Plus, 220–240 V, 50 Hz/230 V, 60 Hz	75009918	Sorvall ST 40R, 230 V (refrigerated)	75004524
Megafuge ST4R Plus-MD, 220 V, 60 Hz	75009618	Sorvall ST4 Plus-MD, 208–240 V, 50/60 Hz	75009509
Multifuge X4 Pro, 208–240 V, 50/60 Hz	75009900	Sorvall ST4R Plus, 220 V, 60 Hz	75009824
Multifuge X4 Pro-MD, 120 V	75009501	Sorvall ST4R Plus-MD, 120 V	75009525
Multifuge X4 Pro-MD, 208–240 V, 50/60 Hz	75009500	Sorvall ST4R Plus-MD, 220 V, 60 Hz	75009624
Multifuge X4R Pro, 220–240 V, 50 Hz/230 V, 60 Hz	75009915	Sorvall X4 Pro, 208–240 V, 50/60 Hz	75009905
Multifuge X4R Pro-MD, 220–240 V, 50 Hz/230 V, 60 Hz	75009515	Sorvall X4 Pro-MD, 120 V	75009506
Multifuge X4R Pro, 220 V, 60 Hz	75009815	Sorvall X4 Pro-MD, 208–240 V, 50/60 Hz	75009505
Multifuge X4R Pro-MD, 120 V	75009516	Sorvall X4R Pro, 220–240 V, 50 Hz/230 V, 60 Hz	75009920
Multifuge X4R Pro-MD, 220 V, 60 Hz	75009615	Sorvall X4R Pro, 220 V, 60 Hz	75009820
Discontinued, previous-generation centrifuges*	Cat. No.		Cat. No.
Megafuge 40, 120 V	75004504	SL 40R, 230 V (refrigerated)	75004527
Megafuge 40, 230 V	75004503	Sorvall Legend XT, 120 V	75004506
Megafuge 40R, 120 V (refrigerated)	75004519	Sorvall Legend XT, 230 V	75004505
Megafuge 40R, 230 V (refrigerated)	75004518	Sorvall Legend XT, 230 V (US and Canada)	75004508
Multifuge X3, 120 V	75004501	Sorvall ST4 Plus, 208–240 V, 50/60 Hz	75009909
Multifuge X3, 230 V	75004500	Sorvall ST4 Plus-MD, 120 V	75009510
Multifuge X3R, 120 V (refrigerated)	75004516	Sorvall ST4R Plus-MD, 220–240 V, 50 Hz/230 V, 60 Hz	75009524
Multifuge X3R, 230 V (refrigerated)	75004515	Sorvall ST4R Plus, 220–240 V, 50Hz/230 V, 60 Hz	75009924
SL 40, 120 V	75004513	Sorvall X4R Pro-MD, 120 V	75009521
SL 40, 230 V	75004512	Sorvall X4R Pro-MD, 220 V, 60 Hz	75009620
SL 40R, 120 V (refrigerated)	75004528	Sorvall X4R Pro-MD, 220–240 V, 50Hz/230 V, 60 Hz	75009520
Discontinued, previous-generation centrifuges**	Cat. No.		Cat. No.
Multifuge 3S Plus, 120 V	75004365	Sorvall Legend T Plus, 120 V	75004367
Multifuge 3S Plus, 230 V	75004361	Sorvall Legend T Plus, 230 V	75004363
Multifuge 3SR Plus, 120 V (refrigerated)	75004375	Sorvall Legend RT Plus, 120 V	75004377
Multifuge 3SR Plus, 230 V (refrigerated)	75004371	Sorvall Legend RT Plus, 230 V (refrigerated)	75004373
Discontinued, previous-generation centrifuges†	Cat. No.		Cat. No.
Fisher Scientific accuSpin Models 3/3R, 120 V	13-100-517	Fisher Scientific accuSpin Models 3/3R, 120 V (refrigerated)	13-100-516

* Compatible with the Thermo Scientific™ TX-750 4 × 750 mL Swinging Bucket Rotor (75003180) and Applied Biosystems™ Bucket for TaqMan® Array Cards (4442571)

** Compatible with the Swing-Out Rotor TTH-750 4 × 750 mL (75006445) or Swing-Out Rotor 4 × 750 mL (75006434) and Applied Biosystems™ Bucket for TaqMan® Array Cards (4337762)

† Compatible with the centrifuge rotor (13-100-518) and Applied Biosystems™ Bucket for TaqMan® Array Cards (4337762)

Find out more at thermofisher.com/taqmanarrays