

Improve your laboratory's productivity and operational efficiency with an evolving solution



Thermo Fisher Scientific™ Amplitude™ Solution version 2.0

1

SOURCE FOR SECURED ASSAY SUPPLY

4

EMPLOYEES FOR OPERATION

100–8,000

TEST RESULTS PER DAY

24/7

PRIORITY SUPPORT*



Flexible sample batching helps decrease test costs and shorten time-to-results



Expanded claim enables use of saliva for less invasive sample collection



Peace of mind in an often chaotic laboratory testing environment



Turnkey technology

50%

of COVID-19 testing is performed on technology from Thermo Fisher Scientific

Applied Biosystems™ TaqPath™ COVID-19 High-Throughput Combo Kit



Accurate, proven, gold-standard technology



Uses a multi-target design to compensate for emerging SARS-CoV-2 variants and mutations



Can signal the presence of the 69-70del S-gene mutation and potentially provide early identification of the Omicron variant (B.1.1.529)

* 365-day, 24/7 priority technical support is available in the English language only. Rapid-response on-site support within 24 hours is subject to regional availability. Regulatory requirements vary by country; products may not be available in your geographic area.

Learn more about the Amplitude Solution at thermofisher.com/amplitude

ThermoFisher
SCIENTIFIC

For Emergency Use Authorization (EUA) Only. For Prescription Use Only. For *In Vitro* Diagnostic Use. © 2021, 2022 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. COL018995 0322