

New Acros Organics Heterocyclic Building Blocks

Heterocyclic Building Blocks			
SKU#	Product Name	Pack size	CAS No.
459280050	N4-Acetylcytosine, 98%	5GR	14631-20-0
459280250		25GR	
459750010	4-Amino-6-hydroxypyrimidine, 98%	1GR	1193-22-2
459750050		5GR	
459820010	1- Aminopiperazine, 98%	1GR	30651-60-6
459822500		250MG	
450040010	6-Amino-2-pyridinemethanol, 97%	1GR	79651-64-2
450040050		5GR	
459760010	4-Aminoquinoline, 95+%	1GR	578-68-7
459762500		250MG	
458820010	4-Azabenzimidazole formate, 97%	1GR	
458820050		5GR	
458450010	4-Azaphthalide, 98%	1GR	5657-51-2
458450050		5GR	
458450250		25GR	
460540050	N4-Benzoylcytosine, 98%	5GR	26661-13-2
460540250		25GR	
449910010	6-Bromoimidazo[1,2-a]pyridine-3-carboxylic acid, 97%	1GR	944896-42-8
449910050		5GR	

Heterocyclic Building Blocks			
SKU#	Product Name	Pack size	CAS No.
458760010	8-Bromoisquinoline, 97%	1GR	63927-22-0
458760050		5GR	
458730010	4-Bromoisoxazole	1GR	97925-43-4
458730050		5GR	
450000010	4-Bromo-2-methoxypyridine, 97%	1GR	100367-39-3
450000050		5GR	
460630010	3-Bromopyrazole, 98%	1GR	14521-80-3
449960010	4-(p-Carboxyphenyl)-1,2,4-triazole, 97%	1GR	157069-48-2
449960050		5GR	
449980010	2-Chloro-4-ethynylpyridine, 97%	1GR	945717-09-9
449980050		5GR	
460030010	4-Chloro-1H-imidazole, 98%	1GR	15965-31-8
459920050	4-Chloropyrazole, 98%	5GR	15878-00-9
459920250		25GR	
450030010	5-Cyclopropyl-1,2,4-oxadiazol-3-amine, 97%	1GR	868696-42-8
450030050		5GR	
459660010	5-Chloropyrimidine, 95%	1GR	17180-94-8
459660050		5GR	
459210250	2,9-Diacetylguanine, 96%	25GR	3056-33-5
459211000		100GR	
459800010	4,6-Diaminopyrimidine, 98%	1GR	2434-56-2
459800050		5GR	
116670250	2,6-Dimethylpiperazine, 98%	25GR	108-49-6
116671000		100GR	

Heterocyclic Building Blocks			
SKU#	Product Name	Pack size	CAS No.
449680010	Ethyl 4-chloro-8-cyanoquinoline-3-carboxylate, 97%	1GR	77173-67-2
449680050		5GR	
449990010	3-Fluoroazetidine hydrochloride, 95%	1GR	617718-46-4
450010010	4-Fluoro-2-methoxypyridine, 97%	1GR	96530-81-3
459410010	6-Hydroxycoumarin, 98%	1GR	6093-68-1
459410050		5GR	
459410250		25GR	
459810010	1H-Indole-2-methanol, 96%	1GR	24621-70-3
459810050		5GR	
459200010	4-Iodo-1-tritylimidazole, 98%	1GR	96797-15-8
459200050		5GR	
458420010	Isothiazole, 97%	1GR	288-16-4
458420050		5GR	
452900010	Lilolidine, 98%	1GR	5840-01-7
452900050		5GR	
459970050	2-Methyl-4-isothiazolin-3-one, 50% Aqueous solution	5GR	2682-20-4
459970250		25GR	
459860010	2-Methylpyrimidine, 98%	1GR	5053-43-0
459860050		5GR	
458070010	2-Methylpyrrolidine hydrochloride, 97%	1GR	54677-53-1
458070050		5GR	
460530010	Morpholin-3-one, 98%	1GR	109-11-5
460530050		5GR	
460530250		25GR	

Heterocyclic Building Blocks

SKU#	Product Name	Pack size	CAS No.
449970010	1-(Pyridin-3-ylmethyl)-1H-pyrazole-4-boronic acid pinacol ester, 97%	1GR	864754-21-2
449970050		5GR	
458980010	2-Pyridin-3-ylpiperidine, 97%	1GR	13078-04-1
458980050		5GR	
450020010	5-Boc-1,4,6,7-tetrahydropyrazolo[4,3-c]pyridine, 97%	1GR	230301-11-8
443970010	4-Thiazolecarboxylic acid, 97%	1GR	3973-08-8
443970050		5GR	
311810010	3,5-Bis(trifluoromethyl)pyrazole, 97%	1GR	14704-41-7

To place an order, contact your local distributor.



©2016 Thermo Fisher Scientific Inc. All rights reserved.
All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

Thermo Fisher Scientific
 ENA 23, Zone 1, nr 1350
 Janssen Pharmaceuticaaan 3a
 2440 Geel
 Belgium
www.acros.com