


| CATALOG NO. | NOMINAL CAPACITY, (oz/mL) |        |         | MATERIALS      |                |
|-------------|---------------------------|--------|---------|----------------|----------------|
|             |                           |        |         | BOTTLE         | CLOSURE        |
| 002750      | 1/8 /4                    | 1/4 /8 | 1/2 /15 | LOPE (NATURAL) | PP (WHITE)     |
| 002751      | 1/8 /4                    | 1/4 /8 | 1/2 /15 | LOPE (WHITE)   | PP (WHITE)     |
| 002752      | 1/8 /4                    | 1/4 /8 | 1/2 /15 | LOPE (NATURAL) | PP (ASSORTED*) |
| 002753      | 1/8 /4                    | 1/4 /8 | 1/2 /15 | LOPE (WHITE)   | PP (ASSORTED*) |

\* (5) EACH; WHITE, RED, GREEN, BLUE, YELLOW

|                        |           |          |           |          |           |           |
|------------------------|-----------|----------|-----------|----------|-----------|-----------|
| SIZE CODE.....:        | -9125     |          | -9025     |          | -9050     |           |
| SIZE (NOM VOL mL/oz)   | 4/ 1/8    |          | 8/ 1/4    |          | 15/ 1/2   |           |
| NOM. BRIM CAP. (mL):   | 6.8       |          | 9.4       |          | 17.9      |           |
| NECK FINISH (mm)....:  | 15        |          | 15        |          | 15        |           |
| THREAD (T.P.I.).....:  | 12        |          | 12        |          | 12        |           |
| NOM. WEIGHT (gms)....: | 4.1       |          | 4.6       |          | 5.6       |           |
|                        | IN.       | mm       | IN.       | mm       | IN.       | mm        |
| D (DIA).....:          | 0.78 ±.03 | 19.7 ±.8 | 0.78 ±.03 | 19.7 ±.8 | 0.96 ±.04 | 24.5 ±1.0 |
| H (HT.).....:          | 2.12 ±.04 | 53.8 ±1  | 2.54 ±.04 | 64.6 ±1  | 2.93 ±.04 | 74.5 ±1   |
| W.T.(MIN. WALL THK):   | .008      | 0.20     | .008      | 0.20     | .008      | 0.20      |



SPECS ON BACK

NOT TO SCALE

- NOTES:
1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
  2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

**ThermoFisher**  
**SCIENTIFIC**

Thermo Fisher Scientific  
75 Panorama Creek Drive  
Rochester, NY 14625-2385, USA

|      |     |         |     |                  |              |
|------|-----|---------|-----|------------------|--------------|
| MADE | ISP | APP'D   | PVC | PSS 00-275X-9XXX | REV.<br>0300 |
| CK'D | GRP | 3/24/00 |     |                  |              |

DESCRIPTION:

DROPPER BOTTLES