


CAT. NO.	NOMINAL SIZES (mL)						MATERIAL
4102	50	125	250	500	1000	2000	PP

SIZE CODE.....:	-0050		-0125		-0250	
SIZE (NOM VOL mL):	50		125		250	
NOM. BRIM CAP. (mL):	55		140		235	
NOM. WEIGHT (gms):	13		31		55	
	INCH	MM	INCH	MM	INCH	MM
A (NECK I.D.):	0.55 ±0.03	14.0 ±0.8	0.66 ±0.03	16.8 ±0.8	0.94 ±0.03	23.9 ±0.8
B (LIP O.D. AT TOP):	0.84 ±0.02	21.3 ±0.5	1.05 ±0.03	26.7 ±0.8	1.37 ±0.03	34.8 ±0.8
C (BODY O.D.):	1.94 ±0.03	49.3 ±0.8	2.67 ±0.04	67.8 ±1.0	3.15 ±0.04	80.0 ±1.0
D (HEIGHT):	3.10 ±0.04	78.7 ±1.0	4.51 ±0.05	114.6 ±1.0	5.13 ±0.05	130.3 ±1.3
W.T.(NOM. WALL THK):	0.07	1.8	0.07	1.8	0.10	2.5

SIZE CODE.....:	-0500		-1000		-2000	
SIZE (NOM VOL mL):	500		1000		2000	
NOM. BRIM CAP. (mL):	610		1120		2200	
NOM. WEIGHT (gms):	100		207		285	
	INCH	MM	INCH	MM	INCH	MM
A (NECK I.D.):	1.18 ±0.03	30.0 ±0.8	1.24 ±0.04	31.5 ±1.0	1.65 ±0.03	41.9 ±0.8
B (LIP O.D. AT TOP):	1.66 ±0.03	42.2 ±0.8	1.96 ±0.03	49.8 ±0.8	2.32 ±0.04	58.9 ±1.0
C (BODY O.D.):	4.20 ±0.05	106.7 ±1.3	5.51 ±0.05	140.0 ±1.3	6.40 ±0.06	162.0 ±1.5
D (HEIGHT):	7.33 ±0.07	186.2 ±1.8	8.44 ±0.08	214.4 ±2.0	10.67 ±0.10	271.0 ±2.5
W.T.(NOM. WALL THK):	0.09	2.3	0.17	4.3	0.17	4.3

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	MCC	APP'D	PVC	PSS 00-4102-XXXX	REV. 0600
CK'D	PVC		6/20/00		

DESCRIPTION:
ERLENMEYER FLASK