

CATALOG NO.	MATERIAL			
	COVER	BASE	STOPCOCK	PLATE
5309-0250	PC	BLUE PP	N/A	(OPTIONAL)*
5310-0250	PC	BLUE PP	BLUE PP BODY & TFE PLUG	(OPTIONAL)*
5315-0150	PC	BLUE PP	N/A	ALUMINUM


* OPTIONAL PLATE CAT. No. 5312-0230

CATALOG NO.....:	5309-0250		5310-0250		5315-0150	
ASSEMBLY WT. (NOM. ,gms).....:	760		790		285	
	INCHES	MM	INCHES	MM	INCHES	MM
A (BASE DIA.).....:	5.6	142	5.6	142	3.7	94
B (COVER O.D.).....:	12.0	305	12.0	305	7.1	180
C (W/ STOPCOCK).....:	N/A	N/A	13.0	330	N/A	N/A
D (BASE I.D.).....:	10.3	262	10.3	262	5.9	150
E (BASE INSIDE HT.):	3.65	92.7	3.65	92.7	1.99	50.5
F (INSIDE).....:	5.7	145	5.7	145	3.46	87.9
G (INSIDE HT.).....:	7.7	196	7.7	196	4.46	113.3
H (OVERALL HT.).....:	9.6	244	9.6	244	5.9	149.9
J (BASE HT.).....:	4.0	102	4.0	102	2.19	55.6

THIS DRAWING IS NOT TO BE REPRODUCED
-CONFIDENTIAL-

NOTES:

- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



DESICCATOR WITH STOPCOCK SHOWN
(CAT. NO. 5310-0250)
NOT TO SCALE

SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	MCC	APP'D PVC	PSS 00-53XX-XXXX-1	REV. 0296
CK'D	PVC	3/11/96		

DESCRIPTION:

DESICCATORS