


	CATALOG NO.		NOMINAL TUBE SIZE, (mm)					MATERIAL	
	005972		13	16	20	25	30	RESMER	
SIZE CODE.....:	SEE BELOW								
MAX. TUBE CAP. (nL):	7.5			15			18		
NOM. WEIGHT (gms):..:	62			118			108		
	INCHES		MM		INCHES		MM		
A (LENGTH).....:	4.06 ±0.05		103.1 ±1.3		4.99 ±0.06		126.7 ±1.5		5.06 ±0.06 128.5 ±1.5
B (WIDTH).....:	4.04 ±0.05		102.6 ±1.3		4.97 ±0.06		126.2 ±1.5		4.06 ±0.05 103.1 ±1.3
C (HEIGHT).....:	2.31 ±0.04		58.7 ±1.0		2.80 ±0.04		71.1 ±1.0		3.34 ±0.04 84.8 ±1.0
D (SQUARE).....:	0.56 ±0.01		14.2 ±0.3		0.68 ±0.02		17.3 ±0.5		0.85 ±0.02 21.6 ±0.5
HOLE ARRAY.....:	6 x 6				6 x 6			4 x 5	
COLOR	SIZE CODE								
WHITE	-0013				-0016			-0020	
BLUE	-0313				-0316			-0320	
GREEN	-0413				-0416			-0420	
RED	-0513				-0516			-0520	

SIZE CODE.....:	SEE BELOW			
MAX. TUBE CAP. (mL):	25		30	
NOM. WEIGHT (gms):..:	120		108	
	INCHES	MM	INCHES	MM
A (LENGTH).....:	4.83 ±0.06	122.7 ±1.5	4.30 ±0.05	109.2 ±1.3
B (WIDTH).....:	4.82 ±0.06	122.4 ±1.5	4.30 ±0.05	109.2 ±1.3
C (HEIGHT).....:	2.95 ±0.04	74.9 ±1.0	3.36 ±0.04	85.3 ±1.0
D (SQUARE).....:	1.03 ±0.02	26.2 ±0.5	1.25 ±0.02	31.8 ±0.5
HOLE ARRAY	4 x 4		3 x 3	
COLOR	SIZE CODE			
WHITE	-0025		-0030	
BLUE	-0325		-0330	
GREEN	-		-0430	
RED	-		-0530	

- NOTES:
- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
 - THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE MC	APP'D PVC	PSS 00-5972-0XXX-1	REV. 0204
CK'D PVC	2/26/04		

DESCRIPTION: UNWIRE HALF-RACKS