


CATALOG NO.....:		155411	
NUMBER OF WELLS.....:		8	
SUGGESTED WORKING VOLUME (mL):		0.2 - 0.4	
CULTURE ARE WELL/cm <sup>2</sup>		0.8	
MATERIAL	MEDIA CHAMBER.....:	POLYSTYRENE	
	COVER.....:	POLYSTYRENE	
	BOTTOM.....:	COVERGLASS	
		INCH	MM
A (MEDIA CHAMBER LENGTH).....:		2.25	57.8
B (MEDIA CHAMBER WIDTH).....:		1.00	25.4
C (COVER LENGTH).....:		1.91	48.5
D (COVER OVERALL LENGTH).....:		2.06	52.3
E (COVER HEIGHT).....:		0.23	5.8
F (COVER WIDTH).....:		0.94	23.9
H (OVERALL HEIGHT).....:		0.51	13.0
W.T. (COVER TYPICAL WALL THICKNESS).....:		0.03	0.8

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher  
SCIENTIFIC

Thermo Fisher Scientific  
75 Panorama Creek Drive  
Rochester, NY 14625-2385, USA

MADE	PB	APP'D	GRP	PSS 155411	REV. 1212
CK'D	KDW	12/4/12			
DESCRIPTION: Lab-Tek CHAMBERED COVERGLASS - 8 WELL					