
CATALOG NUMBER		159933		159934	
RECOMMENDED WORKING VOL:		150		150	
MAXIMUM CAPACITY IN UPRIGHT POSITION (mL)		800		800	
CAP TYPE:		VENT/CLOSE		FILTER	
CULTURE AREA (cm ²)		225		225	
MATERIAL	FLASK:	PS		PS	
	CAP:	BLUE HDPE		BLUE HDPE	
		INCH	MM	INCH	MM
A (NECK I.D.)		1.04	26.4	1.04	26.4
B (LENGTH W/O CAP)		9.06	230.1	9.06	230.1
C (LENGTH W/ CAP):		9.13	231.9	9.13	231.9
D (WIDTH)		5.54	140.7	5.54	140.7
E (HEIGHT)		1.57	39.9	1.57	39.9

- 1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- 2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETORY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

Thermo Fisher SCIENTIFIC

Thermo Fisher Scientific 75 Panorama Creek Drive Rochester, NY 14625-2385, USA

MADE	MC ²	APP'D PVC	PSS 15993X			
CK'D	MP	3/9/06	133 137737			
DESCRI	PTION:	•	2			

EASY FLASK 225CM² WITH CLOSURE