



CATALOG NUMBER.....	SEE BELOW	
NOM. CAP. (uL).....	120	
MATERIAL.....	PS	
	INCH	MM
A (BASE LENGTH).....	5.03	127.8
B (BASE WIDTH).....	3.37	85.5
C (TOP LENGTH).....	4.87	123.7
D (TOP WIDTH).....	3.20	81.3
F (OVERALL HEIGHT).....	0.57	14.4
G DIA.....	0.15	3.7
H (A-1 LOCATION) (X).....	0.48	12.1
J (A-1 LOCATION) (Y).....	0.35	9.0
K (WELL-TO-WELL SPACING)....	.18	4.5
L (WELL DEPTH).....	0.46	11.7
M (BOTTOM OF FILM).....	.07	1.7
*P (LID LENGTH).....	5.02	127.4
*Q (LID WIDTH).....	3.36	85.3
*R (LID HEIGHT).....	.36	9.1
S (STACKED HEIGHT - NO LID):	1.09	27.7
*T (STACKED HEIGHT W/LIDS):	1.33	33.8
*U (ASSEMBLY HEIGHT W/LID):	.665	16.9

CATALOG NO.	SURFACE	COLOR	STERILE	WITH LID*	UNITS/PK/CASE
142761	CELL CULTURE	BLACK	YES	YES	10/30
142762	CELL CULTURE	WHITE	YES	YES	10/30
164730	CELL CULTURE	BLACK	YES	NO	10/30
152041	COLLAGEN I	BLACK	NO	YES	5/20
152029	POLY-D-LYSINE	BLACK	NO	YES	5/20
242763	NON-TREATED	WHITE	NO	NO	10/30
242764	NON-TREATED	BLACK	NO	NO	10/30


* DIM.S APPLY ONLY WHERE "WITH LID" = YES, USING NUNC LID #8337.

NOTES:

- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.




PLATE



LID

NO LID

WITH LID



STACKED ASSEMBLY
SHORT END VIEW

SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE JDD	APP'D PVC	PSS 2427XX	REV. 0207
CHK'D PVC	2/16/07		

DESCRIPTION:

384 WELL, PS, OPTICAL BOTTOM PLATE