


CATALOG NO.	NOMINAL CAPACITY, (oz)							MATERIALS	
								BOTTLE	CLOSURE
002015	1	2	4	8	16	32	64	PC	PP*

*53B CLOSURE - 2000 SIZE IS WHITE PP.

SIZE CODE	-0030		-0060		-0125		-0250	
SIZE (NOM. VOL mL/oz)...	30/1		60/2		125/4		250/8	
NOM. BRIM CAP. (mL).....	45		76		169		318	
NECK FINISH (mm).....	20-415		24-415		38-430		38-430	
THREAD (T.P.I).....	8		8		6		6	
NOM. WEIGHT W/CLOSURE (gms).....	14.5		20		49		60	
	INCHES	MM(REF)	INCHES	MM(REF)	INCHES	MM(REF)	INCHES	MM(REF)
A (NECK I.D).....	0.54±.02	13.7±.5	0.70±.02	17.8±.5	1.12 ±0.025	28.45 ±0.64	1.12 ±0.025	28.45 ±0.64
B (HT. W/CLOSURE).....	2.50±.05	63.5±1.3	3.25±.06	82.6±1.5	4.29±.08	109.2±2.0	5.72±.08	145.3±2.0
C(HT. W/O CLOSURE).....	2.39±.05	60.7±1.3	3.15±.06	80.0±1.5	4.12±.08	104.6±2.0	5.55±.08	141.0±2.0
D (SQUARE).....	1.50±.05	38.1±1.3	1.58±.06	40.1±1.5	2.05±.06	52.1±1.5	2.30±.06	58.4±1.5
W.T. (NOM. WALL THK)....	0.04	1.0	0.04	1.0	0.06	1.5	0.06	1.5

SIZE CODE	-0500		-1000		-2000	
SIZE (NOM. VOL mL/oz)...	500/16		1000/32		2000/64	
NOM. BRIM CAP. (mL)....	595		1210		2380	
NECK FINISH (mm).....	38-430		38-430		53B*	
THREAD (T.P.I).....	6		6		4	
NOM. WEIGHT W/CLOSURE (gms).....	108		170		325	
	INCHES	MM(REF)	INCHES	MM(REF)	INCHES	MM(REF)
A (NECK I.D).....	1.12 ±0.025	28.45 ±0.64	1.12 ±0.025	28.45 ±0.64	1.56 ±0.03	39.62 ±0.8
B (HT. W/CLOSURE).....	6.98±.09	177.3±2.3	8.63±.10	219.2±2.5	10.65±.14	270.5±3.6
C(HT. W/O CLOSURE).....	6.80±.09	172.7±2.3	8.43±.10	214.1±2.5	10.42±.14	264.7±3.6
D (SQUARE).....	2.86±.06	72.64±1.5	3.65±.07	92.7±1.8	4.57±.10	116.1±2.5
W.T. (NOM. WALL THK)....	0.06	1.5	0.05	1.3	0.09	2.3

1.
- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2.
- THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625

DRAWN: MSA	APPROVED: MJR	DRAWING NUMBER: PSS-00-2015-XXXX-1	REV: 3
CHECKED: JHH	DATE: 2/6/2024	DESCRIPTION: SQUARE, NARROW-MOUTH GRADUATED LAB QUALITY BOTTLES	