


CATALOG NO.....:	3103-0015		3103-0050	
MATERIAL.....:	PPCO		PPCO	
SIZE (NOM VOL mL)...:	15		50	
NOM. BRIM CAP. (mL):	16		55	
NOM. WEIGHT(gms)...:	7		15	
	INCH	MM	INCH	MM
A (TOP I.D.).....:	0.59 ±0.01	15.0 ±0.3	1.04 ±0.01	26.4 ±0.3
B (BODY O.D.).....:	0.66 ±0.01	16.8 ±0.3	1.13 ±0.01	28.7 ±0.3
C (HEIGHT).....:	4.67 ±0.02	118.6 ±0.5	5.24 ±0.02	133.1 ±0.5



NOT TO SCALE

SPECS ON BACK

NOT TO SCALE

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE JDD	APP'D BR	PSS 003103-XXXX	REV. 0105
CK'D BR	1/24/05		

DESCRIPTION:
CONICAL CENTRIFUGE TUBES