


CATALOG NO. ....:	3117-0500	
MATERIAL .....	PC	
NOM. CAP. (mL).....:	50	
BRIM CAPACITY (mL)..:	49	
NOM. WT. (gms).....:	17	
	INCHES	MM
A (NECK I.D.).....:	1.02	25.9
B (HEIGHT).....:	4.06	103.1
C (TUBE O.D.).....:	1.134	28.80
W.T. NOM. WALL THK.:	0.058	1.47



SPECS ON BACK

NOT TO SCALE

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

**ThermoFisher**  
**SCIENTIFIC**

Thermo Fisher Scientific  
75 Panorama Creek Drive  
Rochester, NY 14625-2385, USA

MADE	MCC	APP'D	PVC	PSS 00-3117-0500-S	REV.	1094
CK'D	PVC	10/26/94				
DESCRIPTION: 50mL ROUND CENTRIFUGE TUBE						