
CATALOG NO.	NOMINAL CAPACITY, (oz)	MATERIALS	
		JAR	CLOSURE
005005-0015	1/2	PP	HDPE

SIZE (NOM VOL mL/oz)	15/ 1/2		
NOM. BRIM CAP. (mL):	16		
NECK FINISH (mm):	38-415		
THREAD (T.P.I.):	6		
NDM. WEIGHT W/CLOSURE (gms):	14		
	INCH	ММ	
A (NECK I.D.):	1.15 ±0.03	29.2 ±0.8	
B (HT. W/CLOSURE):	1.82 ±0.06	46.2 ±1.5	
C (HT. W/O CLOSURE):	1.68 ±0.06	42.7 ±1.5	
D (DIA):	1.20 ±0.03	30.5 ±0.8	
E (CLOSURE O.D.):	1.66 ±0.04	42.2 ±1.0	
W.T.(NOM. WALL THK):	0.050	1.27	

NOTES:

- 1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- 2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETORY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

Thermofisher SCIENTIFIC

Thermo Fisher Scientific 75 Panorama Creek Drive Rochester, NY 14625, USA

0218

MADE	EJL	APP' D	MJR
CK' D	SA	2/9/1	
DECCRIP	T CIN I		

2/9/18

PSS 00-5005-0015-1

DESCRIPTION:

SPECIMEN CRYDGENIC VIAL