


CATALOG NO.:	5317-0070		5317-0120		5317-0180	
NO. OF SHELVES.....:	2		3		4	
NO. OF GROOVES.....:	3		5		7	
NOM. WEIGHT (lbs)....:	13		22		31	
	IN.	MM	IN.	MM	IN.	MM
A (WIDTH).....:	12	304.8	12	304.8	12	304.8
B (DEPTH WITH HANDLE):	13	330.2	13	330.2	13	330.2
H (HEIGHT).....:	7	177.8	12	304.8	18	457.2
X (INTERNAL WIDTH)....:	11.25 ±.06	285.8 ±1.5	11.25 ±.06	285.8 ±1.5	11.25 ±.06	285.8 ±1.5
Y (INTERNAL DEPTH)....:	11.25 ±.06	285.8 ±1.5	11.25 ±.06	285.8 ±1.5	11.25 ±.06	285.8 ±1.5
Z (INTERNAL HEIGHT)....:	6.25 ±.06	158.8 ±1.5	11.25 ±.06	285.8 ±1.5	17.25 ±.06	438.1 ±1.5

MATERIALS	
BODY.....:	ACRYLIC
SHELVES & TRAY.....:	ACRYLIC
LATCHES & HINGES.....:	STAINLESS STEEL
GASKET.....:	NEOPRENE

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	JDD	APP'D	PSS 00-5317-XXXX-S	REV.
CHK'D	11/26/08	BR		1108

DESCRIPTION:

DESICCATOR CABINETS