
CATALOG NO] :	*3005-42/-70		
SIZE (NOM VOL. (mL):		500		
VOL. AT NECK CAP. (mL):		670		
MATERIALS	BOTTLE	PE ⁻	PETG	
	CLOSURE:	WHIT	TE PP	
	CLOSURE LINER.:	LOPE	FOAM	
NECK FINISH		38-430		
THREAD (T.P.I.):		6		
NDM. WEIGHT W/ CLOSURE (gms)		85		
		INCH	CM	
A (NECK I.D.)		1.11	2.8	
B (HT. W/O CLOSURE):		5.80	17.2	
C (HT. W/	CLOSURE):	6.94	17.6	
D (SQUARE)) :	3.0	7.7	
W.T. (N□M.	WALL THK):	. 020	. 05	

^{* 3005-42} IS LAB-PACK, STERILE 3005-70 IS BULK-PACK, STERILE

NOTES:

- 1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
- 2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



CONFIDENTIAL

THIS PRODUCT SPECIFICATION
SHEET CONTAINS CONFIDENTIAL
AND/OR PROPRIETORY INFORMATION
AND IS TO BE USED ONLY FOR THE
EXPRESSED PURPOSES AGREED UPON
BY AN AUTHORIZED OFFICER OF
THERMO FISHER SCIENTIFIC.

Thermo Fisher SCIENTIFIC

Therno Fisher Scientific 75 Panorama Creek Drive Rochester, NY 14625-2385, USA

MADE	MC ²	APP'D PVC	XX-200E 229	REV.
CK. 0	PVC	1/9/06	L22 2007_VV	0106
OEZCR IE	TION:			
BIOTAINER BOTTLE, PETG, 500ml				