



Chemicals

Top chemicals for the life science and biotech industry

Meet your specific research and manufacturing needs

Offering the following custom services and solutions

Bulk chemical service

We can secure and manage the supply of semi-bulk and bulk volume products using either internal manufacturing or select partners worldwide through our extensive supply-chain network.

Returnable drum program

Ideal choice for handling large quantities of high purity solvents. From lab to production scale, our high volume delivery systems deliver solvents with enhanced safety and improved productivity.

Tailored solvents and solvent blends

Enable customization of solvents to your specifications.

Testing services

Our extensive in-house laboratory, QC capabilities and utilization of accredited external partners allows us to respond quickly to specific quality control testing at your request.

Special solutions

Special aqueous or non-aqueous solutions can be expertly manufactured to your exact specifications.

Customized packaging and labeling

Available in a wide variety of innovative packaging options designed for safety, environmental protection, convenient handling and storage and preservation of product integrity. Complies with all relevant regulations. Custom packaging is also available for chemicals supplied to you.

All products listed below are available for customization based on your needs

Ordering information

Description	CAS number
1,2,6-hexanetriol	106-69-4
1,2-dichloroethane	107-06-2
1-Octanol	111-87-5
2-mercaptoethanol	60-24-2
2-propanol	67-63-0
3-chloroperoxybenzoic acid	937-14-4
Acetic acid	64-19-7
Acetic anhydride	108-24-7
Acetone	67-64-1
Acetonitrile	1975-05-08
Acetonitrile/1% TFA	75-05-8/76-05-1
Acrylamide	1979-06-01
Acrylamide: bisacrylamide	79-06-1/110-26-9
Agar, granulated	-
Agarose	9012-36-6
Ammonium acetate	631-61-8
Ammonium carbonate	506-87-6
Ammonium formate	540-69-2
Ammonium hydroxide	1336-21-6
Ammonium persulfate	7727-54-0
Ammonium phosphate, monobasic	7722-76-1
Ammonium sulfate	7783-20-2
Ampicillin sodium salt	69-52-3
Benzyl alcohol	100-51-6
Bis tris	6976-37-0
Bisacrylamide	110-26-9
Boric acid	10043-35-3
Brij 35	9002-92-0
Brilliant blue G 250	6104-58-1
Brilliant blue R 250	6104-59-2
Bromphenol blue, sodium salt	62625-28-9
Cesium chloride	7647-17-8
CHAPS	75621-03-3
Chloramphenicol	56-75-7
Chlorobenzene	108-90-7
Chloroform	67-66-3
Cyclohexane	110-82-7
Deoxycholic acid, sodium salt	302-95-4
Dimethyl sulfoxide	67-68-5
Dithiothreitol	348-312-3
EDTA, disodium salt	6381-92-6
Ethanol	64-17-5
Ethanol, denatured	-
Ethyl ether, anhydrous	60-29-7
Ethidium bromide	1239-45-8
Ethyl acetate	141-78-6
Formamide	1975-12-07
Formic acid	64-18-6
Glycerol	56-81-5
Glycine	56-40-6
Glycogen	9005-79-2
Guanidine hydrochloride	1950-01-01
Guanidine thiocyanate	593-84-0
HEPES	7365-45-9
Heptafluorobutyric acid	375-22-4
Heptane	142-82-5
Hexanes	110-54-3
Hydrochloric acid	7647-01-0
Imidazole	288-32-4
Iodine	7553-56-2

Description	CAS number
Isooctane	540-84-1
Kanamycin sulfate	25389-94-0
LB agar	-
LB broth	-
Lithium chloride	7447-41-8
Lithium dodecyl sulfate	2044-56-6
Lysozyme	12650-88-3
Methanol	67-56-1
Methyl ethyl ketone	78-93-3
Methyl tert-butyl ether	1634-04-4
Methylene chloride	1975-09-02
Molecular sieves, grade 564	12736-96-8/1332-58-7/14808-60-7
N,N-dimethylformamide	1968-12-02
N-butanol	71-36-3
N-methylpyrrolidone	872-50-4
Pentane	109-66-0
Pepsin	9001-75-6
Peptone	73049-73-7
Phenol	108-95-2
Phosphate buffered saline	-
Potassium acetate	127-08-2
Potassium chloride	7447-40-7
Potassium cyanide	151-50-8
Potassium hydroxide	1310-58-3
Potassium phosphate, dibasic	7758-114
Potassium phosphate, monobasic	7778-77-0
Propionic acid	1979-09-04
Proteinase K	39450-01-6
Pyridine	110-86-1
Sodium acetate, anhydrous	127-09-3
Sodium azide	26628-22-8
Sodium bicarbonate	144-55-8
Sodium chloride	7647-14-5
Sodium citrate dihydrate	6132-043
Sodium dodecyl sulfate	151-21-3
Sodium hydroxide	1310-73-2
Sodium phosphate, dibasic	7558-79-4
Sodium phosphate, dibasic heptahydrate	7782-85-6
Sodium phosphate, monobasic	7558-80-7
Sucrose	57-50-1
Terrific broth	-
Tetrahydrofuran	109-99-9
Toluene	108-88-3
Trichloroacetic acid	1976-03-09
Tricine	5704-041
Triethylamine	121-44-8
Trifluoroacetic acid (TFA)	1976-05-01
Tris base	77-86-1
Tris hydrochloride	1185-53-1
Triton X-100	9002-93-1
Triton X-114	9002-93-1
Trypsin	-
Tryptone	91079-40-2
Tween 20	9005-64-5
Tween 80	9005-65-6
Urea	57-13-6
Water	7732-18-5
Xylene cyanol	4463-44-9
Yeast extract	8013-012
Zinc sulfate heptahydrate	7446-20-0

 Learn more at thermofisher.com/custom-and-bulk
thermo
 scientific | Chemicals