Thermo Scientific Fiberlite H3-LV Rotor



ROTOR SPECIFICATIONS		
Туре	Swinging Bucket	
Material	Carbon Fiber Composit	е
Capacity	2 x 500 mL	
Maximum Speed	3,200 rpm	
Tube Dimensions (mm)	96 x 146	
Angle	90°	
Net Weight	9.25 kg (4.31 lbs.)	
Warranty	15 years	
	RCF	RADIUS
Maximum	1,940 xg	189.0 mm
Minimum	344 xg	84.0 mm

ROTOR AND ACCESSORIES ORDERING INFORMATION

		THERMO SCIENTIFIC SORVALL RC-3 Series	BECKMAN® J6 Series	
Fiberlite H3-LV	Cat. No.	096-028016	096-028015	
	Max. Speed	3,200 rpm	3,200 rpm	
	Max. RCF	1,940 xg	1,940 xg	

LABWARE ORDERING INFORMATION

Tube Vol. (mL)	Vol. Fill (mL)	Description	Cat. No.	Oty. /Pkg.	Tubes /Rotor	Max. Speed (rpm)	Max. RCF (xg)	Dims ØxL (mm)	REQUIRED TUBI Type	E CLOSURES, ADA Cat. No.	APTERS, 1 Oty. /Pkg.	TOOLS & ACCESSORIES Description
500.0	-	Corning® Disposable Conical Tube¹	-	-	2	3,200	1,940	96 x 146	Adapter	018-029023	2	1 place/adapter
250.0	-	Corning Disposable Conical Tube ¹	-	-	4	3,200	1,940	-	Adapter	018-029024	2	1 place/adapter
50.0	-	Nunc™ Disposable Conical Tube	334959	25	20	3,200	1,940	30 x 115	Closure	Included	25	PP Sealing
									Adapter	018-029019	2	10 places/adapter
50.0	-	Corning Disposable Conical Tube ¹	-	-	20	3,200	1,940	_	Adapter	018-029019	2	10 places/adapter
50.0	-	BD Falcon® Disposable Conical Tube¹	-	-	20	3,200	1,940	_	Adapter	018-029019	2	10 places/adapter
15.0	_	Nunc Conical Tube	366036	4	40	3,200	1,940	17 x 120	Closure	Included	50	PP Sealing
									Adapter	018-029018	2	20 places/adapter
15.0	-	Corning Disposable Conical Tube ¹	-	-	40	3,200	1,940	-	Adapter	018-029018	2	20 places/adapter
15.0	-	BD Falcon Disposable Conical Tube ¹	_	-	40	3,200	1,940	_	Adapter	018-029018	2	20 places/adapter
10.0	-	Vacutainer® Tube1	_	-	72	_	_	16 x 100	Adapter	018-029017	2	36 places/adapter
7.0	_	Vacutainer Tube ¹	_	_	72	_	_	_	Adapter	018-029025	2	36 places/adapter
3.0	-	Vacutainer Tube ¹	-	_	60	_	_	-	Adapter	018-029028	2	30 places/adapter

¹ Performance depends upon tube brand. Contact your sales representative for recommended tube manufacturers and further information.



LABWARE ORDERING INFORMATION CONTINUED

									REQUIRED TUBE CLOSURES, ADAPTERS, TOOLS & ACCESSORIES			
Tube Vol. (mL)	Vol. Fill (mL)	Description	Cat. No.	Qty. /Pkg.	Tubes /Rotor	Max. Speed (rpm)	Max. RCF (xg)	Dims ØxL (mm)	Туре	Cat. No.	Qty. /Pkg.	Description
_	-	Standard Microplate	-	-	28	3,200	1,940	10 x 62	Adapter	018-029031	2	14 places/adapter
_	-	Deepwell Microplate	_	-	8	3,200	1,940	_	Adapter	018-029031	2	4 places/adapter
-	-	Promega [®] Slicprep [™] 96 Device ¹	-	-	4	-	-	-	Adapter	018-029032	2	2 places/adapter

^{© 2010} Thermo Fisher Scientific Inc. All rights reserved. Beckman is a registered trademark of Beckman Coulter Inc. Corning is a registered trademark of Corning Inc. BD Falcon and Vacutainer are registered trademarks of BD Bioscience. Promega and Slicprep are registered trademarks of Promega Corp. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.





¹ Performance depends upon tube brand. Contact your sales representative for recommended tube manufacturers and further information.