



Accelerate your Sample measurement

Purchase a new Thermo Scientific™ Orion™ Versa Star Pro™ benchtop meter and receive an additional measurement module!

- pH, ISE, conductivity, or dissolved oxygen measurement modules are automatically recognized by the Versa Star Pro meter and can be added or removed at any time
- Large color display can be personalized to show only the information you need and display one to four measurements simultaneously in any combination
- Setup and calibration designed to be fast and simple with step-by-step instructions and a numeric keypad
- Meter interface available in a variety of languages



Orion Versa Star Pro meters deliver outstanding performance and flexibility in the lab, featuring four channels that can be customized for your measurements.

Limited time savings
Offer ends December 31

Enjoy the versatility a Thermo Scientific Orion Versa Star Pro meter offers for your lab

Purchase a qualifying Versa Star Pro meter or kit from the list below between **July 1, 2017** and **December 31, 2017**.

Visit www.thermofisher.com/freemodule to complete the online redemption form and receive a pH, pH/ISE, conductivity, or dissolved oxygen measurement module for free.

Qualifying Thermo Scientific Orion Versa Star Pro Meters and Kits



Cat. No.	Description
Versa Star Pro pH Meters	
VSTAR10	Meter with pH module
VSTAR12	Meter kit with pH module, 8302BNUMD Thermo Scientific™ Orion™ ROSS Ultra™ Triode™ pH/ATC electrode, Orion Star stirrer probe, ROSS pH buffer and solution kit
VSTAR13	Meter difficult sample kit with pH module, 8172BNWP ROSS Sure-Flow pH electrode, ATC probe, Orion Star stirrer probe, ROSS pH buffer and solution kit
VSTAR80	Meter with pH/LogR module, ATC probe
VSTAR82	Meter kit with pH/LogR module, 8172BNWP Thermo Scientific™ Orion™ ROSS™ Sure-Flow™ pH electrode, ATC probe, ROSS pH buffer and solution kit
VSTAR83	Meter micro sample kit with pH/LogR module, 8220BNWP ROSS Micro pH electrode, ATC probe, ROSS pH buffer and solution kit
Versa Star Pro Conductivity Meters	
VSTAR20	Meter with conductivity module
VSTAR22	Meter kit with conductivity module, 013005MD conductivity probe, 1413μS conductivity standard
VSTAR23	Meter pure water sample kit with conductivity module, 013016MD Orion pure-water conductivity probe with flow-through cell, 100μS conductivity standard
Versa Star Pro Dissolved Oxygen Meters	
VSTAR30	Meter with DO/RDO module
VSTAR32	Meter kit with DO/RDO module, 083005MD DO probe, DO probe maintenance kit, BOD adapter/funnel/stirrer
Versa Star Pro pH/ISE Meters	
VSTAR40A	Meter with pH/ISE module
VSTAR40A2	Meter kit with pH/ISE module, 8102BNUWP ROSS Ultra pH electrode, ATC probe, Orion Star stirrer probe, ROSS pH buffer and solution kit
VSTAR40B	Meter with 2 pH/ISE modules
VSTAR40B2	Meter kit with 2 pH/ISE modules, 8102BNUWP ROSS Ultra pH electrode, ATC probe, Orion Star stirrer probe, ROSS pH buffer and solution kit, second electrode stand
Versa Star Pro pH, Conductivity Meters	
VSTAR50	Meter with pH and conductivity modules
VSTAR52	Meter kit with pH and conductivity modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, ROSS pH buffer and solution kit, 1413μS conductivity standard
Versa Star Pro pH/ISE, Conductivity, Dissolved Oxygen Meters	
VSTAR90	Meter with pH/ISE, conductivity and DO/RDO modules
VSTAR91	Meter with 2 pH/ISE, conductivity and DO/RDO modules
VSTAR92	Meter kit with pH/ISE, conductivity and DO/RDO modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, 083005MD DO probe, Orion Star stirrer probe, ROSS solution kit, 1413μS conductivity standard, DO probe kit, BOD adapter/funnel/stirrer
VSTAR93	Meter kit with 2 pH/ISE, conductivity and DO/RDO modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, 083005MD DO probe, Orion Star stirrer probe, ROSS solution kit, 1413μS conductivity standard, DO probe kit, BOD adapter/funnel/stirrer
VSTAR94	Meter kit with pH/ISE, conductivity and DO/RDO modules, 8157BNUMD ROSS Ultra Triode pH/ATC electrode, 013005MD conductivity probe, 087010MD RDO optical DO probe, Orion Star stirrer probe, ROSS solution kit, 1413μS conductivity standard

The above meters include an electrode stand, universal power adapter, literature and USB cable.

Download complimentary Thermo Scientific™ Orion™ Star Com™ data transfer computer software on our website at thermofisher.com/orionsoftware.

Offer valid only in connection with orders for the product part numbers listed above by customers in the US and Canada (Excludes Puerto Rico) between July 1, 2017 and December 31, 2017. Redemption and proof of purchase required. All redemption requests must be received on or before 5:00PM EST on January 31, 2018, or offer is void. Promotional product shipped separately, and provided subject to manufacturer's standard terms and conditions of sale, available at www.thermofisher.com. Please allow 6-8 weeks for delivery. Not valid in connection with any other offer or discount. Limit 5 promotional product per customer. The promotional items shown at no cost represent an in-kind discount, and should be reported accordingly. Void where prohibited by law or company policy.

Find out more at thermofisher.com/water

Water and Lab Products

North America: 1-978-232-6000 Toll Free: 1-800-225-1480

ThermoFisher
SCIENTIFIC