

Thermo Scientific Precision Water Baths

Precision General Purpose and Circulating Water Bath Accessory Fit Chart

Thermo Scientific™ Precision™ water baths have brought outstanding performance and reliability to laboratories worldwide. Now they are setting a new standard in laboratory water baths, with enhanced designs and added features to help simplify workflows and maximize productivity. This chart recommends the quantity of test tubes, racks, beakers and flasks that will fit best into each Precision general purpose and circulating water bath.

Beakers and Flasks

	General Purpose Water Baths							Circulating and Coliform Water Baths				
	TSGP02	TSGP2S	TSGP05	TSGP10	TSGP20	TSGP28	TSGP15D	TSCIR19	TSCIR35	TSCIR89	TSCOL19	TSCOL35
Beakers (minimum spacing: 2.50cm)												
100mL	1	3	3	12	18	18	15	12	24	66	12	24
150mL	1	3	3	9	15	15	12	12	21	50	12	21
250mL	1	2	2	6	8	8	8	6	14	36	6	14
400mL	1	2	2	4	8	8	6	6	12	32	6	12
Erlenmeyer Flasks (minimum spacing: 2.50cm)												
25mL	1	4	4	16	28	28	20	20	40	78	20	40
50mL	1	3	3	12	18	18	15	12	24	66	12	24
125mL	1	2	2	9	10	10	11	9	21	36	9	21
250mL	1	2	2	4	8	8	6	6	12	32	6	12
500mL	0	2	2	4	6	6	6	4	10	21	4	10
1000mL	0	0	0	1	3	3	1	2	4	10	2	4

Test Tube Racks

Test Tube Diameter (mm)	Rack	Tubes / Rack	General Purpose Water Baths							Circulating and Coliform Water Baths				
			TSGP02	TSGP2S	TSGP05	TSGP10	TSGP20	TSGP28	TSGP15D	TSCIR19	TSCIR35	TSCIR89	TSCOL19	TSCOL35
How many racks fit in my bath?														
13	5972-0013TC	36	1	2	2	6	8	8	8	6	12	32	6	12
16	5972-0016TC	36	0	2	2	4	6	6	6	4	10	18	4	10
20	5972-0020TC	20	0	2	2	4	8	8	6	6	12	24	6	12
25	5972-0025TC	16	0	2	2	4	6	6	6	6	10	21	6	10
30	5972-0030TC	9	0	2	2	4	8	8	6	6	12	28	6	12
13	5970-0513TC	72	0	1	1	3	4	4	4	3	6	16	3	6
16	5970-0516TC	72	0	1	1	2	3	3	3	2	5	9	2	5
20	5970-0520TC	40	0	1	1	3	4	4	4	3	6	12	3	6
25	5970-0525TC	40	0	0	0	2	2	2	2	2	4	7	2	4
30	5970-0530TC	24	0	1	1	2	4	4	3	3	6	12	3	6
How many test tubes is that?														
13	5972-0013TC	36	36	72	72	216	288	288	288	216	432	1152	216	432
16	5972-0016TC	36	0	72	72	144	216	216	216	144	360	648	144	360
20	5972-0020TC	20	0	40	40	80	160	160	120	120	240	480	120	240
25	5972-0025TC	16	0	32	32	64	96	96	96	96	160	336	96	160
30	5972-0030TC	9	0	18	18	36	72	72	54	54	108	252	54	108
13	5970-0513TC	72	0	72	72	216	288	288	288	216	432	1152	216	432
16	5970-0516TC	72	0	72	72	144	216	216	216	144	360	648	144	360
20	5970-0520TC	40	0	40	40	120	160	160	160	120	240	480	120	240
25	5970-0525TC	40	0	0	0	80	80	80	80	80	160	280	80	160
30	5970-0530TC	24	0	24	24	48	96	96	72	72	144	288	72	144

Australia +61 39757 4300
China +800 810 5118
France +33 (0) 1 60 92 48 00
Germany +49 (0) 721 4 09 44 44
India +91 22 6716 2200
Italy +39 02 95059 552
Japan +81-3-6832-9270
Netherlands +31 76 579 55 55

New Zealand +64 9 980 6700
Nordic/Baltic/CIS countries
 +358 10 329 2200
Spain/Portugal +34 93 223 09 18
UK/Ireland +44 870 609 9254
USA/Canada toll free +1 (800) 258-0830
USA +1 (603) 436-9444
Countries not listed +49 6184 90 6000

North America info.tc.us@thermofisher.com
Europe sales.tc.eu@thermofisher.com
China tc.china@thermofisher.com
India LSI_Marketing@thermofisher.com
Japan info.jp.jp@thermofisher.com

Find out more at thermofisher.com/precisionbaths