



Biological safety cabinets

Where innovation meets experience

1500 Series A2 Biological Safety Cabinet

Redefine excellence in your lab with the Thermo Scientific™ 1500 Series Class II, Type A2 Biological Safety Cabinet, offering advanced protection, exceptional user comfort and convenience.

Features include:

- Made in the USA
- Real-time airflow compensation with Thermo Scientific™ SmartFlow™ Plus technology
- Thermo Scientific™ DAVE™ (Digital Airflow Verification) Plus System validates protection by monitoring airflow velocities, which detect and alert to any changes
- User-friendly 7 in. touchscreen interface
- New window mechanism with haptic feedback for correct sash window height
- SmartClean front window design to improve access to the work area for easy cleaning
- Programmable UV light enables pre-scheduled sterilization
- New ergonomic accessories for added comfort
- Stainless-steel, SmartCoat-painted interior

Ordering information

Thermo Scientific 1500 Series Class II, Type A2 Biological Safety Cabinets

Cabinet with manual adjustable stand, UV light, and armrests

Cat. No.	Voltage	Description	China	India & Southeast Asia	Japan	Korea	Taiwan
1593A2	230 V	3 ft (0.9 m), stainless-steel interior, 8" opening, bundle package	x				
1533A2		3 ft (0.9 m), stainless-steel interior, 10" opening, bundle package				x	
1536A2		4 ft (1.2 m), stainless-steel interior, 8" opening, bundle package	x				
1576A2		4 ft (1.2 m), stainless steel interior, 10" opening, bundle package		x		x	
1586A2		4 ft (1.2 m), SmartCoat, 10" opening, bundle package		x			
1578A2		6 ft (1.8 m), stainless-steel interior, 10" opening, bundle package	x	x		x	
1588A2		6 ft (1.8 m), SmartCoat, 10" opening, bundle package		x			
1542A2	120 V	3 ft (0.9 m), stainless-steel interior, 8" opening, bundle package			x		
1523A2		3 ft (0.9 m), stainless-steel interior, 10" opening, bundle package			x		
1535A2		4 ft (1.2 m), stainless-steel interior, 8" opening, bundle package			x		x
1575A2		4 ft (1.2 m), stainless-steel interior, 10" opening, bundle package			x		
1537A2		6 ft (1.8 m), stainless-steel interior, 8" opening, bundle package			x		
1577A2		6 ft (1.8 m), stainless-steel interior, 10" opening, bundle package			x		x
1910282		China Country Configuration	x				
1910280		Hong Kong/ASEAN Country Configuration		x			

The configurations shown are the popular options available for each country. For a comprehensive list of all offerings, please refer to the product brochure or contact us for more information.

 Learn more at thermofisher.com/1500a2-usa

For Laboratory Use. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific use or application. © 2025 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **STUDIO 25-0613**

thermo scientific