

Having trouble viewing this email? [Click here.](#)

Service & Support

Applications & Techniques



Thermo Scientific Liquid Handling Solutions Product Communication

Removal of CE-IVD marking from Thermo Scientific manual pipettes and compatible Thermo Scientific pipette tips

February 28, 2022

Dear Valued Customer,

This letter is to inform you about the upcoming changes in **Thermo Scientific™ Manual Pipettes and their compatible Pipette Tips** related to change in EU regulations.

European IVD Regulation 2017/746 replaces the IVD Directive 98/79/EC in May 2022. Due to this change, **we are removing the CE-IVD marking from our manual pipette portfolio and system tips** (please see all affected SKUs in Appendix I). The new IVD regulation clarifies the product classification and states that pipettes and tips should be “for general laboratory use” products going forward. The change will take place in our production during March 2022.

Multiple European Life Science Organizations (GAMBICA, FHI, LABMAS, Laborama, SPECTARIS) stand behind this reclassification and have prepared a joint statement supporting this. Additionally, majority of the global pipette manufacturers are in alignment with this change.

There will be no change to our product quality, fit and form. We will continue to use the same product codes as currently. The same high standard quality systems will continue to be used in our manufacturing facilities. **These general laboratory use pipettes and tips can continue to be used in all general laboratory applications including IVD as before.**

We thank you for your support of Thermo Scientific products, and we look forward to serving and supporting you through this product change. If you have any questions, please don't hesitate to contact your local sales representative for more information.

Sincerely,

Maiju Palokangas

Sr. Global Product Manager, Pipetting Systems
Liquid Handling Solutions

Appendix I. Product codes affected by the CE-IVD marking removal.

Product Code	Description
Pipettes	
4641010N	Finnpipette F1 0,2-2 µl µTip
4641020N	Finnpipette F1 0,5-5 µl µTip
4641030N	Finnpipette F1 1-10 µl µTip
4641040N	Finnpipette F1 1-10 µl
4641050N	Finnpipette F1 2-20 µl µTip
4641060N	Finnpipette F1 2-20 µl
4641130N	Finnpipette F1 5-50 µl µTip
4641140N	Finnpipette F1 5-50 µl
4641070N	Finnpipette F1 10-100 µl
4641080N	Finnpipette F1 20-200 µl
4641090N	Finnpipette F1 30-300 µl
4641100N	Finnpipette F1 100-1000 µl
4641110N	Finnpipette F1 0,5-5 ml
4641120N	Finnpipette F1 1-10 ml
4651020N	Finnpipette F1 Fixed Volume 10µl
4651130N	Finnpipette F1 Fixed Volume 20µl
4651030N	Finnpipette F1 Fixed Volume 25µl

4651040N	Finnpipette F1 Fixed Volume 50µl
4651050N	Finnpipette F1 Fixed Volume 100µl
4651140N	Finnpipette F1 Fixed Volume 200µl
4651060N	Finnpipette F1 Fixed Volume 250µl
4651070N	Finnpipette F1 Fixed Volume 500µl
4651080N	Finnpipette F1 Fixed Volume 1000µl
4651090N	Finnpipette F1 Fixed Volume 2ml
4651100N	Finnpipette F1 Fixed Volume 3ml
4651110N	Finnpipette F1 Fixed Volume 5ml
4651120N	Finnpipette F1 Fixed Volume 10ml
4661000N	Finnpipette F1 8-ch 1-10µl
4661010N	Finnpipette F1 8-ch 5-50µl
4661020N	Finnpipette F1 8-ch 10-100µl
4661030N	Finnpipette F1 8-ch 30-300µl
4661040N	Finnpipette F1 12-ch 1-10µl
4661050N	Finnpipette F1 12-ch 5-50µl
4661060N	Finnpipette F1 12-ch 10-100µl
4661070N	Finnpipette F1 12-ch 30-300µl
4661080N	Finnpipette F1 16-ch 1-10µl
4661090N	Finnpipette F1 16-ch 5-50µl
4642010	Finnpipette F2 0.2-2µl
4642020	Finnpipette F2 0.5-5µl
4642030	Finnpipette F2 1-10µl µTip
4642040	Finnpipette F2 1-10µl
4642050	Finnpipette F2 2-20µl µTip
4642060	Finnpipette F2 2-20µl
4642120	Finnpipette F2 5-50µl µTip
4642130	Finnpipette F2 5-50µl
4642070	Finnpipette F2 10-100µl
4642080	Finnpipette F2 20-200µl
4642090	Finnpipette F2 100-1000µl
4642100	Finnpipette F2 0.5-5ml
4642110	Finnpipette F2 1-10ml
4652000	Finnpipette F2 Fixed 1µl µTip
4652010	Finnpipette F2 Fixed 5µl µTip
4652020	Finnpipette F2 Fixed 10µl
4652130	Finnpipette F2 Fixed 20µl
4652030	Finnpipette F2 Fixed 25µl
4652040	Finnpipette F2 Fixed 50µl
4652050	Finnpipette F2 Fixed 100µl
4652140	Finnpipette F2 Fixed 200µl
4652060	Finnpipette F2 Fixed 250µl
4652070	Finnpipette F2 Fixed 500µl
4652080	Finnpipette F2 Fixed 1000µl
4652090	Finnpipette F2 Fixed 2ml
4652100	Finnpipette F2 Fixed 3ml
4652150	Finnpipette F2 Fixed 4ml
4652110	Finnpipette F2 Fixed 5ml
4652120	Finnpipette F2 Fixed 10ml
4662000	Finnpipette F2 8-ch 1-10µl
4662010	Finnpipette F2 8-ch 5-50µl
4662020	Finnpipette F2 8-ch 10-100µl

4662030	Finnpipette F2 8-ch 30-300µl
4662040	Finnpipette F2 12-ch 1-10µl
4662050	Finnpipette F2 12-ch 5-50µl
4662060	Finnpipette F2 12-ch 10-100µl
4662070	Finnpipette F2 12-ch 30-300µl
4662080	Finnpipette F2 16-ch 1-10µl
4662090	Finnpipette F2 16-ch 5-50µl
4640000	Finnpipette F3 1-10µl µTip
4640010	Finnpipette F3 1-10µl
4640020	Finnpipette F3 2-20µl µTip
4640030	Finnpipette F3 2-20µl
4640080	Finnpipette F3 5-50µl µTip
4640090	Finnpipette F3 5-50µl
4640040	Finnpipette F3 10-100µl
4640050	Finnpipette F3 20-200µl
4640060	Finnpipette F3 100-1000µl
4640100	Finnpipette F3 0.5-5ml
4640070	Finnpipette F3 1-10ml
4640110	Finnpipette F3 0.2-2µl µTip
4650000	Finnpipette F3 Fixed 1µl µTip
4650010	Finnpipette F3 Fixed 5µl µTip
4650020	Finnpipette F3 Fixed 10µl
4650030	Finnpipette F3 Fixed 25µl
4650040	Finnpipette F3 Fixed 50µl
4650050	Finnpipette F3 Fixed 100µl
4650060	Finnpipette F3 Fixed 250µl
4650070	Finnpipette F3 Fixed 500µl
4650080	Finnpipette F3 Fixed 1000µl
4650090	Finnpipette F3 Fixed 20µl
4650100	Finnpipette F3 Fixed 200µl
4660010	Finnpipette F3 8-ch 5-50µl
4660020	Finnpipette F3 8-ch 30-300µl
4660040	Finnpipette F3 12-ch 5-50µl
4660050	Finnpipette F3 12-ch 30-300µl
4641310N	F1-ClipTip 0.1-2 µl
4641320N	F1-ClipTip, 1-10 µl
4641180N	F1-ClipTip, 2-20 µl
4641190N	F1-ClipTip, 5-50 µl
4641200N	F1-ClipTip, 10-100 µl
4641210N	F1-ClipTip, 20-200 µl
4641220N	F1-ClipTip, 30-300 µl
4641230N	F1-ClipTip, 100-1000 µl
4651280N	F1-ClipTip, Fixed 10 µl
4651200N	F1-ClipTip, Fixed 20 µl
4651210N	F1-ClipTip, Fixed 25 µl
4651220N	F1-ClipTip, Fixed 50 µl
4651230N	F1-ClipTip, Fixed 100 µl
4651240N	F1-ClipTip, Fixed 200 µl
4651250N	F1-ClipTip, Fixed 250 µl
4651260N	F1-ClipTip, Fixed 500 µl
4651270N	F1-ClipTip, Fixed 1000 µl
4661210N	F1-ClipTip 8-ch 1-10 µl

4661120N	F1-ClipTip 8-ch 5-50 µl
4661130N	F1-ClipTip 8-ch 10-100 µl
4661140N	F1-ClipTip 8-ch 30-300 µl
4661220N	F1-ClipTip 12-ch 1-10 µl
4661160N	F1-ClipTip 12-ch 5-50 µl
4661170N	F1-ClipTip 12-ch 10-100 µl
4661180N	F1-ClipTip 12-ch 30-300 µl
Tips	
9400100	Finntip 200 Ext, 400/box
9400130	Finntip 200 Ext, 10x96/rack
9400133	Finntip 200 Ext, 10x96/rack, sterile
9400220	Finntip 250 Universal, 20000/bulk
9400230	Finntip 250 Universal, 1000/bag
9400250	Finntip 250 Universal, 500/box
9400260	Finntip 250 Universal, 10x96/rack
9400263	Finntip 250 Universal, 10x96/rack, sterile
9400266	Finntip 250 Universal, refill starter kit, 10x96/refill+4x96/rack
9400267	Finntip 250 Universal, 20x96/refill kit
9400300	Finntip 10, 10x96/rack
9400303	Finntip 10, 10x96/rack, sterile
9400310	Finntip 10, 1000/bag
9400326	Finntip 10, refill starter kit, 10x192/refill+4x192/rack
9400327	Finntip 10, 20x192/refill kit
9400360	Finntip 50, 1000/bag
9400370	Finntip 50, 10x384/rack
9400373	Finntip 50, 10x384/rack, sterile
9400610	Finntip 20, 10x384/rack
9400613	Finntip 20, 10x384/rack, sterile
9400620	Finntip 20, 1000/bag
9401010	Finntip 1000, 10000/bulk
9401030	Finntip 1000, 1000/bag
9401070	Finntip 1000, 200/box
9401110	Finntip 1000, 10x96/rack
9401113	Finntip 1000, 10x96/rack, sterile
9401115	Finntip 1000, 5x192/refill pack
9401240	Finntip 300, 20000/bulk
9401250	Finntip 300, 10x96/rack
9401253	Finntip 300, 10x96/rack, sterile
9401255	Finntip 300, 10x192/refill pack
9401260	Finntip 300, 1000/bag
9401410	Finntip 1000 Ext, 1000/bag
9401420	Finntip 1000 Ext, 5x96/rack
9401423	Finntip 1000 Ext, 5x96/rack, sterile
9402010	Finntip 5 ml, 3000/bulk
9402030	Finntip 5 ml, 500/bag
9402050	Finntip 5 ml, 75/box
9402070	Finntip 5 ml, 5x54/rack
9402073	Finntip 5 ml, 5x54/rack, sterile
9402150	Finntip 10 ml, 40/box
9402151	Finntip 10 ml, 100/bag
9402160	Finntip 10 ml, 5x24/rack

9402163	Finntip 10 ml, 5x24/rack, sterile
9405020	Finntip 250 Wide, 1000/bag
9405030	Finntip 250 Wide, 22000/bulk
9405050	Finntip 1000 Wide, 400/bag
9405060	Finntip 1000 Wide, 6500/bulk
9405120	Finntip 250 Wide, 10x96/rack
9405123	Finntip 250 Wide, 10x96/rack, sterile
9405160	Finntip 1000 Wide, 10x96/rack
9405163	Finntip 1000 Wide, 10x96/rack, sterile
94052000	Finntip Filter 10µl Micro, 10x96/rack, sterile
94052020	Finntip Filter 20µl, 10x384/rack, sterile
94052060	Finntip Filter 50µl, 10x384/rack, sterile
94052100	Finntip Filter 10µl, 10x96/rack, sterile
94052150	Finntip Filter 20µl, 10x96/rack, sterile
94052160	Finntip Filter 30µl, 10x96/rack, sterile
94052200	Finntip Filter 100µl, 10x96/rack, sterile
94052300	Finntip Filter 200µl, 10x96/rack, sterile
94052310	Finntip Filter 100µl Ext, 10x96/rack, sterile
94052320	Finntip Filter 200µl Ext, 10x96/rack, sterile
94052350	Finntip Filter 300µl, 10x96/rack, sterile
94052410	Finntip Filter 1000µl, 10x96/rack, sterile
94052430	Finntip Filter 1000µl Ext, 5x96/rack, sterile
94052450	Finntip Filter 1500µl 10x96/rack, sterile
94052550	Finntip Filter 5ml, 5x54/rack, sterile
94052600	Finntip Filter 10ml, 5x24/rack, sterile
94056380	Finntip Flex Filter 200µl, 10x96/rack, sterile
94056510	Finntip Flex Filter 30µl, 10x96/rack, sterile
94056520	Finntip Flex Filter 100µl, 10x96/rack, sterile
94056580	Finntip Flex Filter 300µl, 10x96/rack, sterile
94056710	Finntip Flex Filter 1000µl, 10x96/rack, sterile
94056810	Finntip Flex Filter 1200µl, 10x96/rack, sterile
94056970	Finntip Flex Filter 10ml Ext, 50/bag, sterile
94056980	Finntip Flex Filter 10µl, 10x96/rack, sterile
94060100	Finntip Flex 10, 10x96/rack
94060103	Finntip Flex 10, 10x96/rack, sterile
94060116	Finntip Flex 10, refill starter kit, 20x96/refill+1x96/rack
94060117	Finntip Flex 10, 20x96/refill kit
94060120	Finntip Flex 10, 1000/bag
94060310	Finntip Flex 200, 10x96/rack
94060313	Finntip Flex 200, 10x96/rack, sterile
94060316	Finntip Flex 200, refill starter kit, 20x96/refill+1x96/rack
94060317	Finntip Flex 200, 20x96/refill kit
94060320	Finntip Flex 200, 1000/bag
94060510	Finntip Flex 300, 10x96/rack
94060513	Finntip Flex 300, 10x96/rack, sterile
94060516	Finntip Flex 300, refill starter kit, 20x96/refill+1x96/rack
94060517	Finntip Flex 300, 20x96/refill kit
94060520	Finntip Flex 300, 1000/bag
94060710	Finntip Flex 1000, 10x96/rack
94060713	Finntip Flex 1000, 10x96/rack, sterile
94060716	Finntip Flex 1000, refill starter kit, 16x96/refill+1x96/rack
94060717	Finntip Flex 1000, 16x96/refill kit

94060720	Finntip Flex 1000, 1000/bag
94060810	Finntip Flex 1200, 10x96/rack
94060813	Finntip Flex 1200, 10x96/rack, sterile
94060816	Finntip Flex 1200, refill starter kit, 16x96/refill+1x96/rack
94060817	Finntip Flex 1200, 16x96/refill kit
94060820	Finntip Flex 1200, 1000/bag
94060970	Finntip Flex 10 ml Ext, 100/bag
94060973	Finntip Flex 10 ml Ext, 50/bag, sterile
94410210	ClipTip 20, 10x96/rack
94410213	ClipTip 20, 10x96/rack, Sterile
94410217	ClipTip 20 Reload Tower, 10x96/insert
94410218	ClipTip 20 Reload Tower, 10x96/insert, Sterile
94420213	ClipTip 20 Filter, Racked, Sterile
94410250	ClipTip 50, 10x96/rack
94410253	ClipTip 50, 10x96/rack, Sterile
94410257	ClipTip 50 Reload Tower, 10x96/insert
94410258	ClipTip 50 Reload Tower, 10x96/insert, Sterile
94420253	ClipTip 50 Filter, Racked, Sterile
94410310	ClipTip 200, 10x96/rack
94410313	ClipTip 200, 10x96/rack, Sterile
94410317	ClipTip 200 Reload Tower, 10x96/insert
94410318	ClipTip 200 Reload Tower, 10x96/insert, Sterile
94420313	ClipTip 200 Filter, Racked, Sterile
94410510	ClipTip 300, 10x96/rack
94410513	ClipTip 300, 10x96/rack, Sterile
94410517	ClipTip 300 Reload Tower, 10x96/insert
94410518	ClipTip 300 Reload Tower, 10x96/insert, Sterile
94420513	ClipTip 300 Filter, Racked, Sterile
94410710	ClipTip 1000, 8x96/rack
94410713	ClipTip 1000, 8x96/rack, Sterile
94410717	ClipTip 1000, Reload Tower, 8x96/insert
94410718	ClipTip 1000, Reload Tower, 8x96/insert, Sterile
94420713	ClipTip 1000 Filter, 8x96/rack, Sterile
94410060	ClipTip 12.5 Ext, 10x96/rack
94410063	ClipTip 12.5 Ext, 10x96/rack, Sterile
94420063	ClipTip 12.5 Ext Filter, 10x96/rack, Sterile
94410610	ClipTip 300 Ext, 8x96/rack
94410613	ClipTip 300 Ext, 8x96/rack, Sterile
94410617	ClipTip 300 Ext, Reload Tower, 8x96/insert
94410618	ClipTip 300 Ext, Reload Tower, 8x96/insert Sterile
94420613	ClipTip 300 Ext Filter, 8x96/rack, Sterile
94410619	ClipTip 300 Ext Empty Rack



This product is intended for General Laboratory Use. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific use or application.

© 2022 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. We hereby disclose that this email communication is for commercial purposes.
EM5089915



[View our privacy policy.](#)



[thermofisher.com](https://www.thermofisher.com)

ThermoFisher
SCIENTIFIC