

MATERIALS			
CLOSURE		ETFE	
FUNNEL BODY		TEFLON FEP	
STOPCOCK ASSY		TEFLON TFE	
TIP		TEFLON FEP	

CATALOG NUMBER	4301-0125	
NOMINAL VOL. (mL)	125	
NOM. BRIM CAPACITY (mL)	145	
NOMINAL WEIGHT (g)	75	
	INCH	MM (REF)
A (NECK ID)	.77	19.6
B (CLOSURE OD)	1.28	32.5
C (HEIGHT W/CLOSURE)	10.15	257.8
D (HEIGHT W/O CLOSURE)	10.02	254.5
E (OD AT BULB AREA)	2.24	56.9
F (TUBING OD)	.34	8.6
G (MIN WALL THICKNESS)	.02	0.5

CATALOG NUMBER	4301-0250	
NOMINAL VOL. (mL)	250	
NOM. BRIM CAPACITY (mL)	320	
NOMINAL WEIGHT (g)	115	
	INCH	MM (REF)
A (NECK ID)	.93	23.6
B (CLOSURE OD)	1.46	37.1
C (HEIGHT W/CLOSURE)	12.65	321.3
D (HEIGHT W/O CLOSURE)	12.49	317.2
E (OD AT BULB AREA)	3.0	76.2
F (TUBING OD)	.34	8.6
G (MIN WALL THICKNESS)	.02	0.5


CATALOG NUMBER	4301-0500	
NOMINAL VOL. (mL)	500	
NOM. BRIM CAPACITY (mL)	650	
NOMINAL WEIGHT (g)	160	
	INCH	MM (REF)
A (NECK ID)	1.23	31.2
B (CLOSURE OD)	1.855	47.1
C (HEIGHT W/CLOSURE)	13.65	346.7
D (HEIGHT W/O CLOSURE)	13.45	341.6
E (OD AT BULB AREA)	3.76	95.5
F (TUBING OD)	.34	8.6
G (MIN WALL THICKNESS)	.02	0.5

CATALOG NUMBER	4301-1000	
NOMINAL VOL. (mL)	1000	
NOM. BRIM CAPACITY (mL)	1160	
NOMINAL WEIGHT (g)	260	
	INCH	MM (REF)
A (NECK ID)	1.62	41.1
B (CLOSURE OD)	2.26	57.4
C (HEIGHT W/CLOSURE)	14.59	370.6
D (HEIGHT W/O CLOSURE)	14.37	365.0
E (OD AT BULB AREA)	4.70	119.4
F (TUBING OD)	.34	8.6
G (MIN WALL THICKNESS)	.02	0.5

	CATALOG NUMBER	4301-2000	
	NOMINAL VOL. (mL)	2000	
	NOM. BRIM CAPACITY (mL)	2300	
	NOMINAL WEIGHT (g)	370	
		INCH	MM (REF)
	A (NECK ID)	1.59	40.4
	B (CLOSURE OD)	2.26	57.4
	C (HEIGHT W/CLOSURE)	15.79	401.1
	D (HEIGHT W/O CLOSURE)	15.62	396.7
	E (OD AT BULB AREA)	6.21	157.7
	F (TUBING OD)	.34	8.6
	G (MIN WALL THICKNESS)	.02	0.5

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

SPECS ON BACK



NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE PELYCHATY	APP'D 1/13/17	PSS 4301-XXXX	REV. 0117
CK'D JC	PWC		

DESCRIPTION: SEPARATORY FUNNEL