


CATALOG NO.....:	DS4101-0500		DS4101-1000	
MATERIAL.....:	PP		PP	
SIZE (NOM VOL mL).....:	500		1000	
NOM. WEIGHT (gms).....:	135		270	
	INCH	MM	INCH	MM
A (NECK I.D.).....:	1.11 ±.03	28.2 ±0.8	1.25 ±.03	31.8 ±0.8
B (LIP O.D. AT TOP).....:	1.66 ±.03	42.2 ±0.8	1.96 ±.03	49.8 ±0.8
C (BODY O.D).....:	4.20 ±.05	106.7 ±1.3	5.47 ±.05	138.9 ±1.3
D (HEIGHT).....:	7.31 ±.07	185.7 ±1.8	8.43 ±.07	214.1 ±1.8
W.T.(NOM. WALL THK).....:	0.16	4.1	0.10	2.5
FITS STOPPER NO. (NOT INCL.)....:	7		8	

CATALOG NO.....:	DS4101-2000	
MATERIAL.....:	PP	
SIZE (NOM VOL mL).....:	1700	
NOM. WEIGHT (gms).....:	420	
	INCH	MM
A (NECK I.D.).....:	1.65 ±.10	41.9 ±2.5
B (LIP O.D. AT TOP).....:	2.32 ±.04	58.9 ±1.0
C (BODY O.D).....:	6.3 ±.1	160 ±3
D (HEIGHT).....:	10.6 ±.1	269 ±3
W.T.(NOM. WALL THK).....:	0.2	5
FITS STOPPER NO. (NOT INCL.)....:	10	

NOTES:
1. BARBED TUBING ADAPTER ACCEPTS 1/4" AND 3/8" I.D. TUBING.

- NOTES:
- ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
 - THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	MC ²	APP'D	RAL	PSS DS4101-XXXX-1	REV. 0802
CK'D	JDD		8/6/02		
DESCRIPTION: FILTERING FLASK					