

The top of the page features a red horizontal bar with the text "thermoscientific" in white, lowercase letters. Below this bar is a large, abstract graphic composed of various overlapping, rounded shapes in shades of teal, blue, and green, resembling a molecular or network structure. The background of the entire page is a light gray gradient.

thermoscientific

Make Your Comeback

You're ready to return to your lab.
We're here to help you make up for lost time.

ThermoFisher
SCIENTIFIC

Laboratory equipment

Benchtop centrifuges and rotors

- Microcentrifuges to general purpose centrifuges
- Fiberlite carbon fiber rotors

Benchtop laboratory equipment

- Benchtop shakers
- Hotplates and stirrers
- Savant SpeedVac Vacuum Concentrators
- Dry baths

Biological safety cabinets and clean benches

- Herasafe 2030i Class II, A2 BSC
- 1300 Series Class II, A2 BSC
- 1500 Series Class II, B2 BSC
- Heraguard ECO laminar flow hood

CO2 incubators and accessories

- Heracell VIOS 160i/250i CO2 incubator
- Forma Stericult CO2 incubator
- Heracell 150i/240i CO2 incubator
- Forma Stericycle CO2 incubator
- Forma water jacketed CO2 incubator
- Forma 29 cu ft Reach-in CO2 incubator
- Heracell VIOS with Cell Locker system

Constant temperature

- Heratherm Microbiological incubators
- Heratherm Refrigerated incubators
- Forma Environmental chambers
- Ovens and furnaces

Floor centrifuges and rotors

- Sorvall LYNX Superspeed models
- Sorvall WX+ Ultra-speed models
- Large capacity centrifuges
- Low-speed centrifuges
- Fiberlite carbon fiber rotors

Orbital shakers

- Solaris open air shakers
- MaxQ incubated/refrigerated shakers

Cryopreservation systems

- CryoMed, Controlled-rate Freezer
- CryoPlus and CryoExtra auto-fill LN2 Storage
- Locator storage, manual-fill LN2 dewars

Laboratory refrigerators and freezers

- Single, double, and triple door refrigerators (4°C & 5°C)
- Single and double door freezers (-30°C), auto defrost
- Single door enzyme freezers, (-20°C), manual defrost
- Undercounter refrigerators and freezers

Ultra-low freezers, capacity from 300 to 700 boxes

- TSX series -80°C upright freezers
- STP series -40°C and -80°C upright freezers
- 40°C and -80°C chest freezers

Water baths, circulators, and chillers

- Precision water baths
- Heated/refrigerated bath circulators
- Immersion circulators
- Laboratory and recirculating chillers

Remote Monitoring

- Smart-Vue, wireless monitoring system



Water analysis and purification

Water analysis instruments

- Orion Benchtop and Handheld meters
- Electrodes, buffers, and solutions
- Potentiometric titrators
- Colorimetry, turbidity, and spectrophotometry

Water purification

- Barnstead Type 1 Ultrapure Water Purification Systems
- Barnstead Type 2 Pure Water Purification Systems
- Reverse osmosis systems
- Water stills



Laboratory plasticware and supplies

Pipettes

- Manual Pipettes
 - Finnpiquette Single Channel Pipettes
 - Finnpiquette 8-, 12- and 16-Channel Pipettes
 - F1-ClipTip 8- and 12-Channel Pipettes
- Electronic Pipettes
 - Finnpiquette Novus Pipette
 - E1-ClipTip Pipette
 - E1-ClipTip Pipette with Adjustable Tip Spacing
- Pipet Aid
 - S1 Pipet Filler
- Positive Displacement Pipette
 - Finnpiquette Stepper

Pipette Tips and Accessories

- ART Aerosol Barrier Tips
- QSP Universal Tips
 - Standard Tips
 - Low Retention Tips
 - Sterile Filter Tips
- Specialty Tips
 - Extended Length Tips
 - Wide Orifice Tips
 - Gel Loading Tips
 - Individually Wrapped Tips
- Automation Tips
- Reagent Reservoirs

Benchtop Liquid Handling System

- Multidrop Combi Reagent Dispenser
- Multidrop Pico Digital Dispenser

General Labware

- Snap Cap Microtubes
- Screw Cap Microtubes
- Microtube Racks
- Surface Decontaminants
- Wash Bottles
- Beakers/Cylinders/Funnels

Filtration

- Rapid-Flow sterile filters
- Analytical filters and filter funnels
- Syringe filters

Sample storage

- Cryotubes
- 2D Barcoded cryogenic tubes
- Storage plates
- Automated and manual decapping systems (for Cryotubes)
- Cap mats and closures for open top tubes
- Plate heat sealing equipment
- Cryoboxes
- Mr. Frosty™ freezing container

Sample Collection & Packaging

- Micro packaging vials
- Narrow and wide-mouth bottles
- Dropper bottles
- Square bottles
- PET and PETG bottles

Immuno Assay Plates

- Covalent and affinity binding
 - Clear 96-well solid plate
 - Black 96-well plate
 - White 96-well plate
 - Clear strip 96-well plate
- Colorimetric assays and ELISA
 - Clear 96-well solid plate
 - Black 96-well plate
 - White 96-well plate
 - Strip 96-well plate
 - 384-well plate

[Submit Your Interest](#)

Find out more at: [thermofisher.com](https://www.thermofisher.com)

General Enquiries: Laboratory.Products.SEA@thermofisher.com

Singapore Office:

Thermo Fisher Scientific
33 Marsiling Industrial Estate Road 3
#07-06 Singapore 739256

Taiwan Office:

台灣賽默飛世爾科技股份有限公司
11493 台北市內湖區洲子街 85 號
6 樓之1

ThermoFisher
SCIENTIFIC