

# Thermo Scientific Orion Star A111

Basic pH benchtop meter

Thermo Scientific™ Orion™ Star A111 pH Benchtop Meters make it easy and affordable to take simple, accurate pH measurements.




Thermo Scientific Orion Star A111 pH Benchtop Meters combine simplicity with accuracy. A large LCD displays pH or mV readings along with temperature. Icons provide quick updates on battery life, electrode status and calibration information. Simple button layout and onscreen messages help with calibration and setup menu choices.

## Features and Benefits

- Large, informative screen clearly shows the main information, including pH or mV reading, temperature in °C or °F, meter mode, calibration information and power source
- Don't miss a reading—AUTO-READ™ locks in the stable reading on your screen and ready indicator alerts when continuous readings are stable
- Up to 3 point pH calibration with easy recall of calibration point and slope data

- Automatic recognition of USA/NIST and DIN buffers or manual option for custom buffer values
- Non-volatile memory holds up to 50 data points
- Included electrode arm and holder make it easier to maintain and place probes into samples
- Plug the meter into almost any power outlet with the included universal power adapter, or use four AA batteries (sold separately) for added flexibility
- The IP54-rated housing handles splashes and can be wall-mounted if table space is limited
- 3 year meter replacement warranty



**Thermo**  
SCIENTIFIC

## Thermo Scientific Orion Star A111 pH Benchtop Meter

Specifications	
<b>pH</b>	<b>Range:</b> -2.00 to 16.00 <b>Resolution:</b> 0.1, 0.01 <b>Relative Accuracy:</b> $\pm 0.01$ <b>pH Calibration Points:</b> Up to 3
<b>mV</b>	<b>Range—mV:</b> $\pm 1600.0$ mV <b>Range—RmV:</b> $\pm 1999.9$ mV <b>Resolution:</b> 0.1 mV <b>Relative Accuracy:</b> $\pm 0.2$ mV or $\pm 0.05$ % of reading whichever is greater <b>Relative mV Calibration:</b> Yes
<b>Temperature</b>	<b>Range:</b> -5 to 105 °C, 23 to 221 °F <b>Resolution:</b> 0.1 °C, 0.1 °F <b>Relative Accuracy:</b> $\pm 0.1$ °C, $\pm 0.1$ °F <b>Temperature Compensation:</b> Automatic or manual <b>Temperature Offset Calibration:</b> Yes
<b>Datalogging</b>	<b>Number of Points:</b> 50 <b>Log Function:</b> Manual, Automatic with AUTO-READ
<b>Inputs</b>	<b>pH Electrode:</b> BNC <b>ATC Probe:</b> 8-pin mini-DIN
<b>Power</b>	<b>AC Adapter:</b> Included—universal, 100-240 VAC <b>Battery Power:</b> Optional—4 AAs <b>Battery Life:</b> 2000 hrs



Redesigned electrode arm and holder



Thermo Fisher Scientific  
Water Analysis Instruments  
Chelmsford, MA USA  
Quality Management System  
Registered to ISO 9001

[thermoscientific.com/water](http://thermoscientific.com/water)

© 2013 Thermo Fisher Scientific Inc. All rights reserved. Certified System StandardsMark logo is a trademark of SAI Global. All other trademarks are the property of Thermo Fisher Scientific Inc. & its subsidiaries

### Water Analysis Instruments

**North America**  
Toll Free: 1-800-225-1480  
Tel: 1-978-232-6000  
[info.water@thermo.com](mailto:info.water@thermo.com)

**Netherlands**  
Tel: (31) 020-4936270  
[info.water.uk@thermo.com](mailto:info.water.uk@thermo.com)

**China**  
Tel: (86) 21-68654588  
[wai.asia@thermofisher.com](mailto:wai.asia@thermofisher.com)

**India**  
Tel: (91) 22-4157-8800  
[wai.asia@thermofisher.com](mailto:wai.asia@thermofisher.com)

**Singapore**  
Tel: (65) 6778-6876  
[wai.asia@thermofisher.com](mailto:wai.asia@thermofisher.com)

### Meter Ordering Information

Part No.	Description
<b>STARA1110</b>	<b>Orion Star A111 pH Benchtop Meter</b> - Attached electrode stand and holder - Universal power adapter - Printed quick start guide and literature CD
<b>STARA1115</b>	<b>Orion Star A111 pH Benchtop Meter Kit</b> - 9157BNMD Orion Triode refillable, epoxy-body pH/ATC electrode - 916099 Orion 60 mL pH buffer and solutions kit - Attached electrode stand and holder - Universal power adapter - Printed quick start guide and literature CD
<b>STARA1116</b>	<b>Orion Star A111 pH Benchtop Meter TRIS-Compatible Kit</b> - GD9156BNWP Orion Green double junction refillable, epoxy-body pH electrode - 927007MD Orion stainless steel ATC probe - Attached electrode stand and holder - Universal power adapter - Printed quick start guide and literature CD
<b>STARA1117</b>	<b>Orion Star A111 pH Benchtop Meter ROSS Kit</b> - 8157BNUMD Orion ROSS Ultra Triode refillable epoxy-body pH/ATC electrode - 810199 Orion ROSS pH buffer and solutions kit - Attached electrode stand and holder - Universal power adapter - Printed quick start guide and literature CD

### Accessories Ordering Information

Part No.	Description
<b>STARA-BEA</b>	Orion Star A series electrode arm, holder and benchtop meter-attachable base plate
<b>STARA-HB</b>	Orion Star A series freestanding base for electrode arm and holder
<b>9172BNWP</b>	Orion Sure-Flow refillable, glass-body pH electrode
<b>9165BNWP</b>	Orion Sure-Flow refillable, epoxy-body pH electrode
<b>9107BNMD</b>	Orion Triode gel-filled, epoxy-body pH/ATC electrode
<b>927007MD</b>	Orion stainless steel ATC temperature probe
<b>910104</b>	Orion pH 4.01 buffer, 475 mL
<b>910107</b>	Orion pH 7.00 buffer, 475 mL
<b>910110</b>	Orion pH 10.01 buffer, 475 mL
<b>910001</b>	Orion pH electrode storage solution, 475 mL
<b>810001</b>	Orion ROSS pH electrode storage solution, 475 mL
<b>9678BNWP</b>	Orion Sure-Flow refillable epoxy-body ORP electrode
<b>967901</b>	Orion ORP standard solution, 475 mL

For more information, contact your local Thermo Scientific products dealer or call our customer and technical service experts at 1-800-225-1480 (for the US and Canada) or visit [www.thermoscientific.com/water](http://www.thermoscientific.com/water).



**Japan**  
Tel: (81) 045-453-9175  
[wai.asia@thermofisher.com](mailto:wai.asia@thermofisher.com)

**Australia**  
Tel: (613) 9757-4300  
In Australia (1300) 735-295  
[InfoWaterAU@thermofisher.com](mailto:InfoWaterAU@thermofisher.com)

**Thermo**  
SCIENTIFIC

Part of Thermo Fisher Scientific