

**SENSITITRE™ EQUINE PLATE FORMAT**

Plate Code: **EQUIN1F**

	1	2	3	4	5	6	7	8	9	10	11	12
<b>A</b>	AMI 4	AMI 8	AMI 16	AMI 32	AMP 0.25	AMP 0.5	AMP 1	AMP 2	AMP 4	AMP 8	AMP 16	AMP 32
<b>B</b>	AZI 0.25	AZI 0.5	AZI 1	AZI 2	AZI 4	FAZ 4	FAZ 8	FAZ 16	SXT 0.5/9.5	SXT 1/19	SXT 2/38	SXT 4/76
<b>C</b>	XNL 0.25	XNL 0.5	XNL 1	XNL 2	XNL 4	TAZ 1	TAZ 2	TAZ 4	TAZ 8	TAZ 16	TAZ 32	TAZ 64
<b>D</b>	CHL 4	CHL 8	CHL 16	CHL 32	CLA 1	CLA 2	CLA 4	CLA 8	DOX 2	DOX 4	DOX 8	DOX 16
<b>E</b>	ENRO 0.25	ENRO 0.5	ENRO 1	ENRO 2	GEN 1	GEN 2	GEN 4	GEN 8	IMI 1	IMI 2	IMI 4	IMI 8
<b>F</b>	OXA+ 0.25	OXA+ 0.5	OXA+ 1	OXA+ 2	OXA+ 4	ERY 0.25	ERY 0.5	ERY 1	ERY 2	ERY 4	ERY 8	POS
<b>G</b>	PEN 0.06	PEN 0.12	PEN 0.25	PEN 0.5	PEN 1	PEN 2	PEN 4	PEN 8	RIF 1	RIF 2	RIF 4	POS
<b>H</b>	TIC 8	TIC 16	TIC 32	TIC 64	TIM2 8/2	TIM2 16/2	TIM2 32/2	TIM2 64/2	TET 2	TET 4	TET 8	POS

**ANTIMICROBICS**

AMI	Amikacin
AZI	Azithromycin
XNL	Ceftiofur
CHL	Chloramphenicol
ENRO	Enrofloxacin
OXA+	Oxacillin+2%NaCl
PEN	Penicillin
TIC	Ticarcillin
AMP	Ampicillin
CLA	Clarithromycin
GEN	Gentamicin
TIM2	Ticarcillin / clavulanic acid constant 2
FAZ	Cefazolin
TAZ	Ceftazidime
ERY	Erythromycin
SXT	Trimethoprim / sulfamethoxazole
DOX	Doxycycline
IMI	Imipenem
RIF	Rifampin
TET	Tetracycline
POS	Positive Control