

SENSITITRE™ MYCOBACTERIA PLATE FORMAT

Plate Code: **RAPMYCO**

	1	2	3	4	5	6	7	8	9	10	11	12
A	SXT 0.25/4.75	SXT 0.5/9.5	SXT 1/19	SXT 2/38	SXT 4/76	SXT 8/152	LZD 1	LZD 2	LZD 4	LZD 8	LZD 16	LZD 32
B	CIP 0.12	CIP 0.25	CIP 0.5	CIP 1	CIP 2	CIP 4	IMI 2	IMI 4	IMI 8	IMI 16	IMI 32	IMI 64
C	MXF 0.25	MXF 0.5	MXF 1	MXF 2	MXF 4	MXF 8	FEP 1	FEP 2	FEP 4	FEP 8	FEP 16	FEP 32
D	FOX 4	FOX 8	FOX 16	FOX 32	FOX 64	FOX 128	AUG2 2/1	AUG2 4/2	AUG2 8/4	AUG2 16/8	AUG2 32/16	AUG2 64/32
E	AMI 1	AMI 2	AMI 4	AMI 8	AMI 16	AMI 32	AMI 64	AXO 4	AXO 8	AXO 16	AXO 32	AXO 64
F	DOX 0.12	DOX 0.25	DOX 0.5	DOX 1	DOX 2	DOX 4	DOX 8	DOX 16	MIN 1	MIN 2	MIN 4	MIN 8
G	TGC 0.015	TGC 0.03	TGC 0.06	TGC 0.12	TGC 0.25	TGC 0.5	TGC 1	TGC 2	TGC 4	TOB 1	TOB 2	TOB 4
H	CLA 0.06	CLA 0.12	CLA 0.25	CLA 0.5	CLA 1	CLA 2	CLA 4	CLA 8	CLA 16	TOB 8	TOB 16	POS

ANTIMICROBICS

SXT	Trimethoprim / sulfamethoxazole
CIP	Ciprofloxacin
MXF	Moxifloxacin
FOX	Cefoxitin
AMI	Amikacin
DOX	Doxycycline
TGC	Tigecycline
CLA	Clarithromycin
LZD	Linezolid
IMI	Imipenem
FEP	Cefepime
AUG2	Amoxicillin / clavulanic acid 2:1 ratio
AXO	Ceftriaxone
MIN	Minocycline
TOB	Tobramycin
POS	Positive Control