Acros Organics BV (Thermo Fisher Scientific)
Janssen Pharmaceuticalaan 3a
Geel,
2440, Belgium

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	43358
Lot Number	A0473438
Description	1,2-Dichloroethane,99.8%,for HPLC
CAS Number	107-06-2
Quality Test/Release Date	12/Jun/2025
Suggested retest date	12/Jun/2028
Country of Origin	UNITED KINGDOM
Declaration of Origin	synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Appearance (Form)		Clear liquid	Clear liquid
Color scale	APHA	=<10	=<10
GC	%	>=99.75	99.98
Water	%	=<0.02	0.01
Acidity/alkalinity	meq/g	=<0.0003	=<0.0003
Residue after evaporation	ppm	=<2	=<2
UV		at 230 nm A: =<1.00	at 230 nm A:0.48
UV		at 240 nm A: =<0.15	at 240 nm A:0.08
UV		at 250 nm A: =<0.05	at 250 nm A:0.01
UV		at 260 nm A: =<0.005	at 260 nm A:0.0047
UV		at 270 nm A: =<0.005	at 270 nm A:0.005



Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.