

Product Name: Phosphoric acid, 85% w/w aq. soln., ACS, Thermo Scientific™
Catalog Number: 033266.A1

CAS Number: 7664-38-2
IUPAC Name: phosphoric acid
Molecular Formula: H₃O₄P
Molecular Weight: 97.99
InChI Key: NBIIXXVUZAFBLC-UHFFFAOYSA-N
SMILES: OP(O)(O)=O
Synonym: phosphoric acid fosforzuuroplossingen sodium dihydrogen orthophosphate phosphate ion (PO₄³⁻) caswell no. 662 concise etchant wc-reiniger marphos K-etchant trihydroxidooxidophosphorus

Product Specification

Impurity content: Fe 0.003%
Impurity content: Na 0.025%
Impurity content: Reducing substances P.T.
Impurity content: SO₄ 0.003%
Impurity content: As 1ppm
Impurity content: Cl 3ppm
Impurity content: K 0.005%
Impurity content: Mn 0.5ppm
Impurity content: NO₃ 5ppm
Impurity content: Sb 0.002%
Insoluble material: 0.001%
Assay (unspecified): 85.0% H₃O₄P min
Impurity content: Ca 0.002%
Impurity content: Volatile acids (as CH₃COOH) 0.001%
Trace Metals: (as Pb) 0.001%
Color (APHA): 10
Impurity content: Mg 0.002%

Date Of Print: 05/17/2024

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.