

Product Name: Dichloromethane, anhydrous, 99.7+%, packaged under Argon in resealable ChemSeal™ bottles, stab. with amylene, Thermo Scientific Chemicals

Catalog Number: 041835.AK

CAS Number: 75-09-2

IUPAC Name: dichloromethane

Molecular Formula: CH₂Cl₂

Molecular Weight: 84.93

MDL Number: MFCD00000881

InChI Key: YMWUJEATGCHHMB-UHFFFAOYSA-N

SMILES: ClCCl

Synonym: methylene chloridelmethylene dichloridelchloride, methylenelmethylenchloridchlorure de methylenelaerothene MMImethylene bichloridelsolmethinelsolaesthinInarkotil

Product Specification

Water Content (Karl Fischer Titration): 0.01% max

Residue on Evaporation: 3 ppm. Max

Assay (GC): 99.7% min

Date Of Print: 05/17/2024

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.