

Product Name: Dichloromethane, Environmental Grade, 99.8+%, stab. with amylene

Catalog Number: 042006.K2

CAS Number: 75-09-2

IUPAC Name: dichloromethane

Molecular Formula: CH₂Cl₂

Molecular Weight: 84.93

MDL Number: MFCD00000881

InChI Key: YMWUJEATGCHHMB-UHFFFAOYSA-N

SMILES: ClCCl

Synonym: methylene chloridelmethylene dichloridelchloride, methylenelmethylenchloridchlorure de methylenelaerothene MMImethylene bichloridelsolmethinelsolaesthinInarkotil

Product Specification

Form: Clear liquid

Assay (GC): ≥99.8%

Impurity content: 10 ppt, max- GC-ECD responsive residue (single peak) as heptachlorepoide

Impurity content: Cholide: 10ppm, max

Water Content (Karl Fischer Titration): 0.02%, max

Residue on Evaporation: 3ppm, max

Color (APHA): 10, max

Stabilizer: 40-200ppm amylenes

Date Of Print: 05/08/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.