

Product Name: Dimethyl sulfoxide, HPLC grade, 99.9+%, packaged under Argon in resealable AcroSeal™ bottles

Catalog Number: 047330.AE

CAS Number: 67-68-5

IUPAC Name: methanesulfinylmethane

Molecular Formula: C₂H₆OS

Molecular Weight: 78.13

InChI Key: IAZDPXIOMUYVGZ-UHFFFAOYSA-N

SMILES: CS(C)=O

Synonym: dimethyl sulfoxide infiltrina DMSO doligur rimso 100 demasorb caswell no. 381 dolicur dmso - dimethylsulphoxide rimso-50

Product Specification

Appearance (Color): Clear colorless

Form: Liquid

Optical Absorbance at: 350 nm: ≤0.02 AU

Residue on Evaporation: ≤5 ppm

Assay from Supplier's CofA: ≥99.9% (GC)

Optical Absorbance at: 268 nm: ≤1.00 AU

Optical Absorbance at: 300 nm: ≤0.20 AU

Optical Absorbance at: 400 nm: ≤0.005 AU

Optical Absorbance at: 275 nm: ≤0.50 AU

Water Content (Karl Fischer Titration): ≤0.1%

Date Of Print: 05/16/2024

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.