

Product Name: Quinaldic acid, 98%
Catalog Number: A10192.14

CAS Number: 93-10-7
IUPAC Name: quinoline-2-carboxylic acid
Molecular Formula: C₁₀H₇NO₂
Molecular Weight: 173.17
InChI Key: LOAUVZALPPNFOQ-UHFFFAOYSA-N
SMILES: OC(=O)C1=CC=C2C=CC=CC2=N1
Synonym: quinaldic acid 2-chinolincarbonsaeure 2-quinolinyicarboxylate quinaldinate
 chinaldinsaeure quinaldinic acid 2-quinolinyicarboxylic acid

Product Specification

Appearance (Color): White to cream or pale yellow or pale brown
Form: Crystals or powder or crystalline powder
Assay (Aqueous acid-base Titration): ≥97.5 to ≤102.5%
Assay (Silylated GC): ≥97.5%
Melting Point (clear melt): 153.5-160.5°C

Date Of Print: 09/24/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.