

**Product Name:** Oxalic acid dihydrate, 98%  
**Catalog Number:** A13866.0B

---

**CAS Number:** 6153-56-6  
**IUPAC Name:** oxalic acid dihydrate  
**Molecular Formula:** C<sub>2</sub>H<sub>2</sub>O<sub>6</sub>  
**Molecular Weight:** 126.06  
**InChI Key:** GEVPUGOOGXGPIU-UHFFFAOYSA-N  
**SMILES:** O.O.OCC(=O)C(=O)O  
**Synonym:** oxalic acid dihydrate

### Product Specification

**Appearance (Color):** White  
**Form:** Crystals or powder or crystalline powder  
**Melting Point (clear melt):** 98-106°C  
**Assay (Aqueous acid-base Titration):** ≥97.5 to ≤102.5%  
**Identification (FTIR):** Conforms

---

**Date Of Print:** 07/15/2025

*Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.*