

Product Name: 4-Bromophenylacetic acid, 99%
Catalog Number: A15325.14

CAS Number: 1878-68-8
IUPAC Name: 2-(4-bromophenyl)acetic acid
Molecular Formula: C₈H₇BrO₂
Molecular Weight: 215.05
InChI Key: QOWSWEBLNVACCL-UHFFFAOYSA-N
SMILES: OC(=O)CC1=CC=C(Br)C=C1
Synonym: C₈H₇BrO₂ P-bromophenylacetic acid

Product Specification

Appearance (Color): White to pale cream
Form: Crystals or powder or crystalline powder
Assay (Aqueous acid-base Titration): ≥98.5 to ≤101.5%
Assay (Silylated GC): ≥98.5%
Melting Point (clear melt): 113.0-120.0°C

Date Of Print: 04/24/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.