

Product Name: 10-Undecenoic acid, 99%

Catalog Number: A19122.0B

CAS Number: 112-38-9

IUPAC Name: undec-10-enoic acid

Molecular Formula: C₁₁H₂₀O₂

Molecular Weight: 184.28

InChI Key: FRPZMMHWLSIFAZ-UHFFFAOYSA-N

SMILES: OC(=O)CCCCCCCCC=C

Synonym: desenex 10-undecylenic acid acide 10-undecylique caswell no. 901 ω-hendecenoic acid
acido 10-undecenoico renselin hendecenoic acid, ω- cruex 10-undecensaeure

Product Specification

Appearance (Color): Colorless to white to pale yellow

Form: Fused solid or clear liquid as melt

Assay (Aqueous acid-base ≥98.5 to ≤101.5%

Titration):

Assay (GC): ≥97.0%

Identification (FTIR): Conforms

Date Of Print: 05/17/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.