

**Product Name:** 3-Hydroxy-2-naphthoic acid, 98%  
**Catalog Number:** A19214.0B

**CAS Number:** 92-70-6  
**IUPAC Name:** 3-hydroxynaphthalene-2-carboxylic acid  
**Molecular Formula:** C<sub>11</sub>H<sub>8</sub>O<sub>3</sub>  
**Molecular Weight:** 188.18  
**InChI Key:** ALKYHXVLJMQRLQ-UHFFFAOYSA-N  
**SMILES:** OC(=O)C1=C(O)C=C2C=CC=CC2=C1  
**Synonym:** BONA bon acid miketazol developer ons C.I. developer 20 (obs.) kyselina  
 3-hydroxy-2-naftoova BON C.I. developer 20 naphthol B.O.N. CI developer 20  
 3-hydroxy-2-naphthoesaeure

## Product Specification

**Appearance (Color):** Yellow to pale brown  
**Form:** Powder  
**Assay (Aqueous acid-base Titration):** ≥97.5 to ≤102.5%  
**Melting Point (clear melt):** 218-229°C  
**Assay (HPLC):** ≥97.5%

**Date Of Print:** 06/21/2025

*Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.*