

Product Name: 1,3-Di-o-tolylguanidine, 99%
Catalog Number: B25127.22

CAS Number: 97-39-2
IUPAC Name: N,N''-bis(2-methylphenyl)guanidine
Molecular Formula: C₁₅H₁₇N₃
Molecular Weight: 239.32
InChI Key: OPNUROKCUBTKLF-UHFFFAOYSA-N
SMILES: CC1=CC=CC=C1NC(N)=NC1=CC=CC=C1C
Synonym: ditolylguanidine

Product Specification

Appearance (Color): White to cream
Form: Powder
Assay (Non-aqueous acid-base Titration): ≥98.5 to ≤101.5%
Melting Point (clear melt): 171.0-177.0°C

Date Of Print: 05/28/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.